

OGA DIAGONAL: 18.25 [463.63]
VA DIAGONAL: 17.54 [445.50]
PA DIAGONAL: 16.54 [420.12]



TOP LEVEL NUMBER	SKU 98 NUMBER	TYPE	DIM "A" (TOTAL GLASS TO CONNECTOR)	A/G FINISH	PROD SPEC
17-8421-203	98-0003-2589-8	FFC	4.27" [108.46]	AG500	23655
17-8421-221	98-0003-2596-3	SER	4.27" [108.46]	AG500	23655
17-8421-204	98-0003-2590-6	FFC	6.00" [152.40]	AG500	23655
17-8421-223	98-0003-2597-1	SER	6.00" [152.40]	AG500	23655
17-8421-227	98-0003-2599-7	SER	8.00" [203.20]	AG500	23655
17-8421-205	98-0003-2591-4	FFC	8.00" [203.20]	AG500	23655
17-8421-206	98-0003-2190-5	NOV	SEE DWG	AG500	23655
17-8421-218	98-0003-2594-8	USB R	4.27" [108.46]	AG500	23655
17-8421-220	98-0003-3151-6	USB R	6.00" [152.40]	AG500	23655
17-8421-226	98-0003-3152-4	USB R	8.00" [203.20]	AG500	23655
17-8421-230	98-0003-2276-2	HID M	8.00" [203.20]	AG500	23655
N/A	98-0003-3537-6	HID D	8.00" [203.20]	AG500	23655

(HID D)
EXII-7740HC
98-0003-3065-8
HID CONTROLLER
SOLDER SIDE


(HID M)
EXII-7730HC
98-0003-2813-2
HID CONTROLLER
SOLDER SIDE

(USB R)
EXII-7760UC
98-0003-2814-0
USB CONTROLLER
SOLDER SIDE

(SER)
EXII-7720SC
98-0003-2217-6
SERIAL CONTROLLER
SOLDER SIDE



.147±.020 [3.73±.51]
TOTAL THICKNESS
OF GLASS, CABLE
AND STRAIN RELIEF



NOTES:

1. WEIGHT OF GLASS IN GRAMS: 804±10%
2. 5 PIN AMP CONNECTOR
LATCH STYLE HOUSING P/N: 487526-4
TIN CONTACTS P/N: 2-487406-4
HOUSING ORIENTED WITH LATCH DOWN

PINOUT	
1	LL
2	UL
3	SHLD
4	UR
5	LR

UNITS	INCHES [MM]	3M TOUCH SYSTEMS METHUEN, MA USA
TOLERANCES UNLESS OTHERWISE SPECIFIED		
.X	±	
.XX	±.03 [.76]	
.XXX	±.015 [.38]	
ANGLES	±1°	
THIRD ANGLE PROJECTION		
DO NOT SCALE DRAWING		
SCALE	1 = 1	

07	REVISED PER CO 031180	11/09	SEB
06	REVISED PER CO 030452	5/09	SB
05	REVISED PER CO 028945	5/08	SEB
REV	CHANGE NOTICE	DATE	DRW
TITLE			
MARKETING DRAWING SCT32NN 17.54"			
CNO FORMAT		SHEET 1 OF 1	
SIZE	DOCUMENT NO.	REV	
C	28165-MKT	07	