


TIMING & SYNCHRONIZATION

- ▶ Synchronization Systems
- ▶ System Clocks & Frequency References
- ▶ Mature Timing & Synchronization
- ▶ GPS Disciplined Oscillators (GPSDO)
- ▶ Clock Management
 - Numerically Controlled Oscillator
 - ▶ Frequency Conversion & Jitter Attenuation
 - ▶ Clock Synthesis/Generation
 - ▶ Clock Fan-out Buffers
 - ZL40200,ZL40201
 - ZL40202,ZL40203
 - ZL40204,ZL40205
 - ZL40206,ZL40207
 - ZL40208,ZL40209
 - ZL40210,ZL40211
 - ZL40212,ZL40213
 - ZL40214,ZL40215
 - ZL40216,ZL40217
 - ZL40218,ZL40219
 - ZL40220,ZL40221
 - ZL40222,ZL40223
 - ZL40224,ZL40225
 - ZL40226,ZL40227
 - **ZL40230,ZL40235,ZL40240**
 - ZL40231,ZL40234,ZL40241,ZL40260
 - ZL40250,ZL40251,ZL40252,ZL40253
 - ZL40255
- ▶ Embedded Atomic Clocks
- ▶ Precision Crystal & SAW Oscillators
- ▶ Network Synchronization ICs
- ▶ Timing Accessories



Home / Timing & Synchronization / Clock Management / Clock Fan-out Buffers / ZL40230,ZL40235,ZL40240 / Timing & Synchronization / Timing & Synchronization / Clock Management / Clock Fan-out Buffers / ZL40230,ZL40235,ZL40240 / Clock Management / Timing & Synchronization / Clock Management / Clock Fan-out Buffers / ZL40230,ZL40235,ZL40240 / Clock Fan-out Buffers / Timing & Synchronization / Clock Management / Clock Fan-out Buffers / ZL40230,ZL40235,ZL40240 / ZL40230,ZL40235,ZL40240 / Timing & Synchronization / Clock Management / Clock Fan-out Buffers / ZL40230,ZL40235,ZL40240 / ZL40230LDF1

ZL40230LDF1

Product Status

■ In Production

ZL40230,ZL40235,ZL40240

Overview

Resources

Diagrams

Ordering

Support

miSmartBuffer Clock Fan-Out Buffers



ROHS

Package Tape & Reel
Carrier:

Electrical Rating	Symbol	Min	Typ	Max	Unit
CMOS Outputs	CMOSout			1	outputs
Differential Outputs	Diffout			10	outputs

This part can be found in the following product categories:

- Timing & Synchronization ▶ Clock Management
- Timing & Synchronization ▶ Clock Management ▶ Clock Fan-out Buffers ▶ ZL40230,ZL40235,ZL40240
- Timing & Synchronization ▶ Clock Management ▶ Clock Fan-out Buffers