


This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, & that no right is granted to disclose or to use any information in this document.



Customer drawing

POSITION	A	B	C	D	E	F(PITCH)
9	16.24	24.99	39.40	20.00	28.20	2.77
15	24.60	33.32	47.70	28.00	36.50	2.77
25	38.38	47.04	64.50	41.50	51.00	2.77
37	54.76	63.50	80.78	57.80	67.30	2.77

REVISIONS				
SYM	ECN	DESCRIPTION	DATE	APPROVED
2		ADD PN. of 10u" Au	2/29/12	IP

D-SUB TECHNICAL DATA

SHELL : Steel, 1.25um(50u") min nickel

BODY : Glass filled thermoplastic.
flame retardant to UL94 V-0 color Black

PLATE : Glass filled thermoplastic.
flame retardant to UL94 V-0 color Black

CONTACTS : Brass, gold over 50u" min nickel.(According to the P/N)

SCREWLOCK : Brass, 50u" min nickel

REAR INSERT : Brass, 50u" min nickel

O RING : Silicone Color: Blue

EPOXY: Color: Black

ELECTRICAL : Voltage rating: 300 V/RMS at 50Hz
Current rating : 5A
Insulation resistance >5000 MOhms
Contact resistance 20 mOhms max.

MARKING : Amphenol logo
Commercial code
Manufacturing date(YYWW)



NOTE : Screw L=4.7 For Panel Thickness
Under X=1.2mm
Screw L=5.7 For Panel Thickness
Between X=1.2~2.0mm

PRODUCT CODE

L 17ED XX S 0 X

L: RoHS Compliance


17ED:
standard density series

Number of contacts
Standard density:
09, 15, 25, 37

Contact plating:
0: gold flash
1: 0.38um(15u")
2: 0.76um(30u")
4: 0.25um(10u")

Termination:
0: Solder cup

Contact type
S: Socket

UNLESS OTHERWISE SPECIFIED TOLERANCES U.S. METRIC .X +/- 0.50 .XX +/- 0.30 .XXX +/- 0.20 FRACTIONS +/- ANGLES +/- 2' FOR MATERIALS AND FINISHES SEE NOTES REMOVE SHARP EDGES DIMENSIONS U.S. INCHES METRIC MM 		APPROVAL		DATE		Amphenol Amphenol East Asia Limited 	
---	--	----------	--	------	--	---	--