


Copyright FCI.


FCIconnect.com

PRODUCT NUMBER	PITCH
KSxx01x000J0G	7.62 mm









RECOMMENDED P.C.B LAYOUT
TOP VIEW

Material:
- Item ⓐ Left Cover :Thermoplastic (UL94 - V0)
- Item ⓑ Middel Body :Thermoplastic (UL94 - V0)
- Item ⓒ Right Cover :Thermoplastic (UL94 - V0)
- Item ⓓ Pin: Copper Tin plated
- Item ⓔ Wire guard:Stainless Steel (ET 7.62)

Electrical: cULus
- Voltage rating: 300V
- Current rating: 41A
- Withstanding Voltage:1.6 KV
- Operating temperature:-40°C to +115°C
- Soldering temperature:260°C±5°C/5 Sec
- Safety approval: cULus

N=Number of poles

Dim L	N × 7.62
Dim P	(N-1) × 7.62

Dimension

Poles	Tolerance
2P-5P	±0.20
6P-8P	±0.30
9P-12P	±0.35
13P-16P	±0.40

PART NO.: K S xx 0 1 x 0 00J0 G

End stackable No. of poles
02 2 poles
03 3 poles
... ...
16 16 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant (lead<4%) In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK PLUGGABLE PLUG,WITH SOLDER PIN,VERTICAL
				angles	linear X.±0.5 / X.X±0.3 / X.XX±0.1	MM	
				X°±1°		scale	
				dr EVIN ZHONG 050614			dwg no KSxx01x000J0G sheet 1 of 1 size A4
				engr EVIN ZHONG 050614			
				chr HANKE FENG 050614			type CUSTOMER Drawing
				appd SHI JUN 050614			
sheet index	revision A / sheet 1						

Downloaded from Arrow.com.