© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

CONNECTORS

HEADERS & RECEPTACLES



✔ Active

TE CONNECTIVITY (TE)

CT RELAY HDR ASSY 6P BLACK

AMP CT | AMP CT

6-292254-6
TE Internal Number: 6-292254-6

EU RoHS Compliant
EU ELV Compliant

Connector System Wire-to-Board, Wire-to-Panel, Wire-to-Wire

Number of Positions 6

Centerline (Pitch) (mm) 2

Number of Rows 1

Contact Mating Area Plating Material Tin

PRODUCT DRAWING
English

3D PDF

DOCUMENTATION

Product Drawings

PANEL MOUNT TYPE RELAY POST HEADER ASS'Y (AMP CT CONNECTOR 2mm PITCH)
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP
English

Downloaded from Arrow.com.

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Specifications

Product Specification

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

TIF

Japanese

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

PDF

Japanese

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Connector System Wire-to-Board, Wire-to-Panel, Wire-to-Wire
Header Type Feed Through, Shrouded
Sealable No
Product Type Connector
Connector Type Header
Shape Rectangular
Connector Style Plug
Wire/Cable Type Discrete Wire

Configuration Features

Number of Positions 6
Number of Rows 1
Backwall/Post Interruptions Without

Electrical Characteristics

Operating Voltage (VAC) 125
Operating Voltage (VDC) 125

Contact Features

Downloaded from Arrow.com.

Contact Shape Round
Contact Mating Area Plating Material Tin
Contact Mating Area Plating Thickness 1 µm [39.37 µin]
Contact Current Rating (Max) (A) 4
Contact Base Material Brass
Contact Termination Area Plating Material Tin
Contact Transmits (Typical) Signal (Data)
Contact Design Round Post
Tail Plating Material Tin
Contact Type Pin

Mechanical Attachment

Panel Mount Retention With
Mating Retention Without
Connector Mounting Type Panel
Mating Alignment With
Mating Retention Type Locking Latch
Mating Alignment Type Polarization
Contact Retention Without

Housing Features

Centerline (Pitch) (mm) 2
Housing Material Nylon 66
Housing Color Black

Dimensions

Height 12 mm [.472 in]
Width 6 mm [.236 in]
Length 15.78 mm [.621 in]
Wire/Cable Size (AWG) 30 – 22
Mating Post Length 4.5 mm [.177 in]

Usage Conditions

Operating Temperature Range -40 – 105 °C [-40 – 105 °F]

Operation/Application

Pick and Place Cover Internal
For Use With MT Connector

Industry Standards

Agency/Standard UL 94V-0, UL
CSA File Number LR 7189
UL Flammability Rating UL 94V-0
Agency/Standard Number CSA, UL
UL File Number E28476

Packaging Features

Packaging Reel Diameter 300
Packaging Method Bag/Box
Packaging Quantity 300

PRODUCT COMPLIANCE

Downloaded from Arrow.com.

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.