



Part Number : [347928080](#)
Product Description : Mini50 Unsealed Vertical Header, Single Row, 8 Circuit, Polarization Option A, Black, Tape and Reel
Series Number : 34792
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[347928080 sd.pdf](#)
[PK-47799-0001-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[AS-34791-020-CH-001.pdf](#)
[2065230000-AS-000.pdf](#)
[AS-34791-020-001.pdf](#)
[AS-34791-020-CH-001.pdf](#)
[AS-34791-020-FR-001.pdf](#)
[2065230000-AS-KR-000.pdf](#)
[PS-34791-020-001.pdf](#)
[2065230000-TS-000.pdf](#)
[347910020-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 33
China RoHS	

	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	34792
Description	Mini50 Unsealed Vertical Header, Single Row, 8 Circuit, Polarization Option A, Black, Tape and Reel
Application	Automotive, Power, Signal, Wire-to-Board
Component Type	PCB Header
Product Name	Mini50
UPC	889056918718

Electrical

Current - Maximum per Contact	4.0A (for reference only)
-------------------------------	---------------------------

Voltage - Maximum	14V (typical operating)
-------------------	-------------------------

Physical

Breakaway	No
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	1.500/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	Yes
PC Tail Length	2.90mm
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	Through Hole

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mini50 Unsealed Receptacle Housings	<u>34791</u>
Mini50 Unsealed Dual Row	<u>206523</u>

Receptacles	
-------------	--

This document was generated on Sep 24, 2025