

MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH-BASIC

CATALOG LISTING

BZ-2RW8761-A2

APQ7425

BZ-2RW8761-A2

M

DRAWING
NUMBER

6

ISSUE

REPLACES X87680-BZ

RELEASE NO. PR-16607

CHECK

REVISIONS

A	CO64100	
S	D	MAR 89
B	CO-73287-D	
K	D R	8 JULY 93
C	CO-77589	
MAM		29 MAR 94
D	CO93346	
DLT		2 SEP 98
E	0015139	
TSG		23 AUG 05

RJ

CHECK

4 AUG 88


CHECK DES

TLB 4 AUG 88

FORMTEK

FO-52848-A

DRAWN




NOTE



MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE-----6 OZ MAX

RELEASE FORCE-----1 1/2 OZ MIN

DIFFERENTIAL TRAVEL-----.004-.025

OVERTRAVEL-----.141 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P D T

L74 15A 125, 250, OR 480VAC 2A 600 VAC
1/8 HP 125 VAC, 1/4 HP 250 VAC
1/2A 125 VDC, 1/4A 250 VDC

-L288-
-L306-
-L315-
CE EN 05 EC 71 16A 250V T85 5E4

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES

APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE:

	DIM. mm	TOL. mm/in	DIM. in	TOL. mm/in
NO PLACES	X	1/.04	X	0.01/03
ONE PLACE	X,X	0.4/.016	X,X	0.38/.016
TWO PLACES	X,X,X	0.16/.008	X,X,X	0.13/.008
THREE PLACES	X,X,X,X		X,X,X,X	

DESIGN UNITS ☐ SI METRIC ☐ US CUSTOMARY

WEIGHT .073 LB.