

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0009071028
Status: Obsolete
Overview: kk
Description: 3.96mm (.156") KK® IDT Double Cantilever Contact, 2 Circuits, Tin (Sn), Feed-To, 20 Solid or Fused Stranded, and 18 Stranded, Red ID Strip

Documents:
[Drawing \(PDF\)](#)

Agency Certification
UL E29179


General
Product Family IDT and Solder Connectors
Series 7675
Comments Double Cantilever contact
Crimp Quality Equipment Yes
Overview kk
Product Name KK®

Physical
Circuits (Loaded) 2
Color - Resin Natural
Flammability 94V-2
Gender Female
Glow-Wire Compliant No
Lock to Mating Part None
Material - Metal Brass
Material - Resin Nylon
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 3.96mm (.156")
Temperature Range - Operating 0°C to +75°C
Termination Interface: Style IDT or Pierce
Wire Size AWG 18 Stranded, 20 Solid, 20 Stranded Topcoat

Electrical
Voltage - Maximum 250V

Material Info
Old Part Number A-7675-C02M

Reference - Drawing Numbers
Product Specification PS-7660
Sales Drawing SDA-7675-****



Series
image - Reference only

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
7675Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Insertion Tool for 3.96mm (.156") Pitch KK® IDT Crimp Terminals	0638133503
IDT - Manual Press For Ribbon Cable	0011200314
IDT - Semi-automatic - Bench-Top Terminator	0011200418
IDT - Manual Handtool	0011215196
IDT Manual Handtool Arbor Press Fixture	0621000400 0690200770

This document was generated on 05/10/2011

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION