









NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, BLACK
- FRAME: STEEL; NICKEL PLATED
- FLOAT MOUNTS: COPPER ALLOY; NICKEL PLATED
- RIVETED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- CONNECTOR WILL BE SUPPLIED WITHOUT CONTACTS
- CONNECTOR IS PART MARKED: DSS5XSXXB01X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale:		2:1 (5:1)					
							material:		SEE NOTES					
				DO NOT ALTER CAD DRAWING BY HAND						date	name		title: D-SUB FEMALE 50pos. CRIMP STYLE with frame and float mount	
										drawn	24.08.05	Schmidt		
						appd.	24.08.05	Mickenbecker						
						norm			dwg no: 16K1A1488					
						d-old								
4 x b		Ä5047	16.01.2014	Lehm.			part no: DSS5XSXXB01X							
a		Original		DIN-A3										
rev.		description	date	name					sh: 1					

CONEC