Part Number : 1200698486
Product Description : Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
Series Number : 120069
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Part Number : 804S01BS1M050



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120069
Description	Micro-Change (M12) Single-Ended Cordset with Knurled Hexnut, 4 Poles, A-Coded, Female (90°) to Pigtail, 22 AWG, Black TPU WSOR Cable, 5.0m (16.40') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Protocol	N/A
Type	Single Ended
UPC	887191719160

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	60V

Physical

Cable Diameter	5.70mm (.224")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Knurled Hexnut, Threaded

Downloaded from Arrow.com.

Gender	Female-Pigtail
Keyway	A-Coded
LED Indicator	None
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	259.200/g
Orientation	90° to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	22

Downloaded from Arrow.com.