









APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/27/18	
A		UPDATE SPEC.	6/27/19	AY/TW



SECTION A-A



ASSEMBLY VIEW

SPECIFICATIONS:

Material:

Insulator: Hi-temp thermoplastic, rated UL 94V-0

Insulator color: Black

Contacts: Brass

Plating:

Matte Tin over Copper underplate overall

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 3 A AC/DC

Contact resistance: 20 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Temperature Rating:

-25° to +85°

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 12

A = .100 [2.54] x No. of Spaces

B = .100 [2.54] x No. of Spaces + .397 [10.09]

C = .100 [2.54] x No. of Spaces + .200 [5.09]

D = .100 [2.54] x No. of Spaces + .120 [3.05]

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

APPROVALS		DATE
DRAWN	HR	7/27/18
CHECKED	RC1	7/27/18
APPROVED		

ADAM
TECH
 INTERCONNECTS

909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

TITLE 1.00 [2.54] WAFER, STRAIGHT, MATTE TIN PLATED			
SIZE X	PART NO. CDR-D-XX-MTS-P-HT	REV. A	
REF: S00186T	SCALE: NTS	SHEET 1 OF 1	