NEUTRIK



# NC7MD-LX

7 pole male receptacle, solder cups, Nickel housing, silver contacts

The DLX series features a compact all metal housing with an ingenious duplex ground contact, which offers excellent RF protection and shielding.

## Features & Benefits

- All metal housing offers best overall RF protection and electromagnetic shielding
- Duplex ground contact for excellent contact integrity between chassis and cable connector
- Male connector's retention bar replaces plastic design with all metal version improving pull-out force
- Larger solder contacts for easier termination
- Optional connection to easily join pin1 to chassis ground
- D-style housing provides installation compatibility with industry standard D mounting dimensions

## Technical Information

| Product | |
|---|---|
| Title | NC7MD-LX |
| Connection Type | XLR |
| Gender | male |


All rights reserved / 25.08.2026


Downloaded from Arrow.com.

NEUTRIK

| Electrical | |
|---|---|
| Capacitance between contacts | ≤ 9 pF |
| Contact resistance | ≤ 5 mΩ |
| Dielectric strength | 1,5 kVdc |
| Insulation resistance | > 10 GΩ (initial) |
| Rated current per contact | 5 A |
| Rated voltage | < 50 V |

| Mechanical | |
|---|---|
| Insertion force | ≤ 20 N |
| Withdrawal force | ≤ 20 N |
| Lifetime | > 1000 mating cycles |
| Wiresize | max. 1.0 mm² |
| Wiresize | max. 18 AWG |
| Wiring | Solder contacts |
| Locking device | Latch lock |
| Chassis shape | D |

| Material | |
|---|---|
| Contact plating | 2 µm Ag |
| Contacts | Brass (CuZn35Pb2) |
| Insert | Polyamide (PA 6.6 30 % GR) |
| Locking element | Steel Ck67 |
| Shell | Zinc diecast (ZnAl4Cu1) |
| Shell plating | Nickel |


All rights reserved / 25.08.2026


Downloaded from Arrow.com.

| Environmental | |
|---|---|
| Flammability | UL 94 HB |
| Standard compliance | IEC 61076-2-103 |
| Protection class | IP 40 |
| Solderability | Complies with IEC 68-2-20 |
| Temperature range | -30 °C to +80 °C |


All rights reserved / 25.08.2026


Downloaded from Arrow.com.