

NTE597 Silicon Rectifier Ultra Fast, 200V, 8A

Description:

The NTE597 is a silicon rectifier in a 2-Lead TO220 type package designed for use in switching power supplies, inverters and as free wheeling diodes.

Features:

- Ultrafast 50ns Recovery Time
- 175°C Operating Junction Temperature
- Popular TO220 Package
- Epoxy meets UL94, V_O @ 1/8"
- Low Forward Voltage
- Low Leakage Current
- High Temperature Glass Passivated Junction

Absolute Maximum Ratings:

Peak Repetitive Reverse Voltage, V_{RRM} 200V
 Working Peak Reverse Voltage, V_{RWM} 200V
 DC Blocking Voltage, V_R 200V
 Average Rectified Forward Current (Total Device, V_R = 200V, T_C = +150°C), I_{F(AV)} 8A
 Peak Repetitive Forward Current (V_R = 200V, Square Wave, 20kHz, T_C = +150°C), I_{FM} 16A
 Non-Repetitive Peak Surge Current, I_{FSM}
 (Surge applied at rated load conditions halfwave, single phase, 60Hz) 100A
 Operating Junction Temperature Range, T_J -65° to +175°C
 Storage Temperature Range, T_{stg} -65° to +175°C
 Maximum Thermal Resistance, Junction-to-Case, R_{thJC} 2.0°C/W

Electrical Characteristics:

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Instantaneous Forward Voltage	V _F	i _F = 8A, T _C = +150°C, Note 1	—	—	1.0	V
		i _F = 8A, T _C = +25°C, Note 1	—	—	1.3	V
Instantaneous Reverse Current	i _R	V _R = 200V, T _C = +150°C, Note 1	—	—	500	μA
		V _R = 200V, T _C = +25°C, Note 1	—	—	10	μA
Reverse Recovery Time	t _{rr}	I _F = 1A, di/dt = 50A/μs	—	—	60	ns
		I _F = 0.5A, i _R = 1A, I _{REC} = 0.25A	—	—	50	ns

Note 1. Pulse Test: Pulse Width = 300μs, Duty Cycle ≤ 2.0%

