

## SEK-18 SV MA STD STR45 RKZ 14P PL3



Image is for illustration purposes only. Please refer to product description.

### Identification

Category	Connectors
Series	SEK Standard
Element	Male connector
Description of the contact	Straight

### Version

Termination method	Wave soldering termination
Connection type	PCB to cable
Number of contacts	14
Termination length	4.5 mm
Locking type	With short levers

### Technical characteristics

Contact rows	2
Contact spacing (termination side)	2.54 mm
Rated current	1 A
Insulation resistance	$>10^9 \Omega$
Contact resistance	$\leq 20 \text{ m}\Omega$
Limiting temperature	-55 ... +125 °C
Insertion force	$\leq 42 \text{ N}$
Withdrawal force	$\leq 42 \text{ N}$
Performance level	3 acc. to IEC 60603-13

## Technical characteristics

Mating cycles	≥50
Test voltage U <sub>r.m.s.</sub>	1 kV
Isolation group	IIIa (175 ≤ CTI < 400)

## Material properties

Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Grey
Material (contacts)	Copper alloy
Surface (contacts)	Noble metal over Ni Mating side Sn over Ni Termination side
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

Specifications	IEC 60603-13
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
Railway classification	F3/I3

## Commercial data

Packaging size	100
Net weight	6.91 g
Country of origin	Romania
European customs tariff number	85366990
GTIN	5713140028388

Page 2 / 3 | Creation date 2025-05-13 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application.

HARTING Electronics GmbH | Marienwerderstraße 3 | 32339 Espelkamp | Germany  
Phone +49 5772 47-97200 | [electronics@HARTING.com](mailto:electronics@HARTING.com) | [www.HARTING.com](http://www.HARTING.com)

## Commercial data

eCl@ss 27460201 PCB connector (board connector)

ETIM EC002637

UNSPSC 24.0 39121415

## Cross section of solder termination

