


Data Sheet | Item Number: 713-1406/107-000


THT male header, 2-row; 0.8 x 0.8 mm solder pin; straight; 100% protected against mismatching; Threaded flange; Pin spacing 3.5 mm; 12-pole; black

<https://www.wago.com/713-1406/107-000>





Color: ■ black

Similar to illustration



Dimensions in mm
 $L = [(pole\ no./2) - 1] \times pin\ spacing + 13.6\ mm$



Stiftleiste Serie 713, schwarz

Die Stiftleiste hat die Artikelnummer 713-1406/107-000 und verspricht eine saubere ordentliche Elektroinstallation. Setzen Sie beim Design-In Ihres Gerätes auf erprobte Sicherheit: Mit Leiterplatten-Steckverbindern haben Sie verschiedene Verwendungsmöglichkeiten. Die Maße sind in Breite x Höhe x Tiefe (31,1 x 17,3 x 13,3) mm. Für die Kontaktoberfläche wurde Zinn eingesetzt. Das MCS – "Multi Connection System" von WAGO umfasst insgesamt 7 Familien in den Rastermaßen 2,5 mm bis 10,16 mm und bietet mit dem Leiterquerschnittsbereich von 0,08 bis 25 mm² ein großes Portfolio an Einsatzmöglichkeiten. Die Verlötlung des Leiterplatten-Steckverbinders erfolgt mittels THT.

Notes	
Safety Information	The MCS – MULTI CONNECTION SYSTEM includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors must not be connected/disconnected when live or under load. When used as intended, these connectors must not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.
Variants:	Other pole numbers Other solder pin lengths Gold-plated or partially gold-plated contact surfaces Other versions (or variants) can be requested from WAGO Sales or configured at https://configurator.wago.com/ .



Electrical data

Ratings per IEC/EN 60664-1				Approvals per UL 1059			
Overvoltage category	III	III	II	Use group	B	C	D
Pollution degree	3	2	2	Rated voltage	150 V	50 V	-
Nominal voltage	80 V	160 V	250 V	Rated current	10 A	10 A	-
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV				
Rated current	10 A	10 A	10 A				

Approvals per CSA			
Use group	B	C	D
Rated voltage	150 V	-	-
Rated current	12 A	-	-

Connection data

Total number of potentials	12	Connection 1	
Number of connection types	1	Pole number	12
Number of levels	2		

Physical data

Pin spacing	3.5 mm / 0.138 inches
Width	31.1 mm / 1.224 inches
Height	17.3 mm / 0.681 inches
Height from the surface	13.5 mm / 0.531 inches
Depth	13.3 mm / 0.524 inches
Solder pin length	3.8 mm
Solder pin dimensions	0.8 x 0.8 mm
Drilled hole diameter with tolerance	1.2 ^(+0.1) mm

Mechanical data

Variable coding	Yes
Anti-rotation protection	Yes

Plug-in connection

Contact type (pluggable connector)	Male connector/plug
Connector (connection type)	for PCB
Mismating protection	Yes
Mating direction to the PCB	90 °
Locking of plug-in connection	Threaded flange

PCB contact

PCB contact	THT
Solder pin arrangement	over the entire male connector (in-line)
Number of solder pins per potential	1



Material data	
Note (material data)	Information on material specifications can be found here
Color	black
Material group	I
Insulation material (main housing)	Polyphthalamide (PPA GF)
Flammability class per UL94	V0
Contact material	Electrolytic copper (E _{CU})
Contact Plating	Tin
Fire load	0.076 MJ
Weight	3.8 g

Environmental requirements	
Limit temperature range	-60 ... +100 °C
Processing temperature	-35 ... +60 °C

Commercial data	
Product Group	3 (Multi Conn. System)
PU (SPU)	25 pcs
Packaging type	Box
Country of origin	PL
GTIN	4045454808952
Customs tariff number	85366930000

Product classification	
UNSPSC	39121409
eCl@ss 10.0	27-44-04-02
eCl@ss 9.0	27-44-04-02
ETIM 9.0	EC002637
ETIM 8.0	EC002637
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
CAS-No.	7439-92-1
REACH Candidate List Substance	Lead
RoHS Compliance Status	Compliant,With Exemption
RoHS Exemption	6(c)
SCIP notification number (Austria)	797bb49f-b9bc-4aa2-8dec-2ade56297ccb
SCIP notification number (Belgium)	8ed51492-9653-4a95-a944-48909c6f2104
SCIP notification number (Bulgaria)	71ceff77-ab04-41bc-9830-c9b0cf700438
SCIP notification number (Czech Republic)	0d32da67-eca5-4f7f-a8e6-24be646e64eb
SCIP notification number (Denmark)	be8b3c21-661a-4d94-a896-8001f25e8d40
SCIP notification number (Finland)	8c44a701-344d-43cc-a9ee-848f397fff38
SCIP notification number (France)	a1bc0472-9a15-4555-bf55-4892bb0c7d92
SCIP notification number (Germany)	589309dd-230f-4e0c-b032-20e982f6a457
SCIP notification number (Hungary)	b28a73aa-48fb-4f24-9116-b1db4a75ba16
SCIP notification number (Italy)	4ef26e93-a63d-4973-bc6c-d18bb285115e
SCIP notification number (Netherlands)	6b301d76-ba5e-405c-b512-62dd4def192a
SCIP notification number (Poland)	640f567c-c01f-477e-8a89-dc30f3aadd84
SCIP notification number (Romania)	945f042e-f4ea-4beb-be87-f792dfed1da2
SCIP notification number (Sweden)	8b63dc80-d470-4ea5-9687-ff97939c1b04



Approvals / Certificates

General approvals



Approval	Standard	Certificate Name
CB DEKRA Certification B.V.	IEC 61984	NL-102427
CSA CSA Group	C22.2	2315087
KEMA/KEUR DEKRA Certification B.V.	EN 61984	71-133740
UL Underwriters Laboratories Inc.	UL 1059	UL-US-L45172-6187124-22905991-1

Downloads

Environmental Product Compliance

Compliance Search
Environmental Product Compliance 713-1406/107-000



Documentation

Additional Information
Technical Section
03.04.2019
pdf 2027.26 KB



CAD/CAE-Data

CAD data
2D/3D Models 713-1406/107-000



CAE data
ZUKEN Portal 713-1406/107-000



PCB Design
Symbol and Footprint via SamacSys 713-1406/107-000
Symbol and Footprint via Ultra Librarian 713-1406/107-000



1 Compatible Products

1.1 System counterpart

1.1.1 Female connector/socket



Item No.: 713-1106/107-000
1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 12-pole; 100% protected against mismatching; Screw flange; 1,50 mm²; black



Item No.: 713-1106/107-047
1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 12-pole; 100% protected against mismatching; Screw flange; direct marking; 1,50 mm²; black



Item No.: 713-1106/107-9037
1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 12-pole; 100% protected against mismatching; Screw flange; direct marking; 1,50 mm²; black



Item No.: 713-1106/107-000/036-000
1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 12-pole; 100% protected against mismatching; Screw flange; Strain relief plate; 1,50 mm²; black



Item No.: 713-1106/107-9037/032-000
1-conductor female connector, 2-row; CAGE CLAMP®; 1.5 mm²; Pin spacing 3.5 mm; 12-pole; 100% protected against mismatching; Screw flange; Strain relief plate; direct marking; 1,50 mm²; black

1.2 Optional Accessories

1.2.1 Coding


1.2.1.1 Coding



Item No.: 714-101
Coding key; orange

Installation Notes

Coding



Coding a male header by inserting a coding pin.