

CATALOG LISTING
7AS12
PAGE 1 OF 1
ISSUE 11
REPLACES
CHECK
REVISIONS
A CO-70985
MAM
6 DEC 93
B CO-93073
DIT
22 JUL 98
C CO-92864
TSM
3 NOV 98
CHECK
7 DEC 93
CHECK
A W
CHECK
6 DEC 93
DRAWN
MAM
DDM/CAD

MICRO SWITCH
a Honeywell Division
FED. MFG. CODE 91929

ASSEMBLY – SWITCH



CATALOG LISTING
7AS12
KS-G0120
FAA-PMA

MECHANISM IN POSITION NO. 1

POSITION OF SHAFT	SWITCH ACTUATED N.O. TO COM. MADE
1	NONE
2	1

2X 6-32 UNC THREAD LOCKING TYPE HEX NUT .31 ACROSS FLATS


DETENT SPRING





2X HEX NUT

2X LOCKWASHER

2X ROUND HEAD MACHINE SCREW



3X 4-40 UNC X (.125) ROUND HEAD TERMINAL SCREW AND LOCKWASHER



FLEXIBLE INSULATOR

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH. A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION
CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
	15.1A 1/2HP 125, 250 VAC 1/2A 125 VDC, 1/4A 250 VDC 5A 125 VAC "L"	UNLESS OTHERWISE SPECIFIED TOLERANCES ARE
		ONE PLACE (.0) ± .030 TWO PLACE (.00) ± .015 THREE PLACE (.000) ± .005 ANGLES ± 3° WEIGHT

- NOTES
- 1 – UNIT INCLUDES CATALOG LISTING V3-201 BASIC SWITCH
- 2 – SWITCH WILL PERFORM SATISFACTORILY IN TEMPERATURES TO MINUS 20°F
- 3 – CATALOG LISTING, DATE OF MANUFACTURE AND FAA-PMA IS MARKED ON BRACKET

ANSI Y14.5M-1982 APPLIES