

ComboLock® 1.00mm Signal pitch and 3.00mm Power pitch Hand Tool

PROFESSIONAL, FAST & ROBUST

The FCI Basics' crimping hand tool is professionally designed for applications in the prototyping phase or small production quantities. The hand tool has a mechanism which opens automatically after making the last advance of the ratchet. There are 2 different tools depending on the wire gauge needed.

These hand tools are dedicated for the ComboLock® 1.00/3.00 mm Crimp-to-Wire product.

ComboLock® is a compact, hybrid wire-to-board connector system that saves space, allows for simpler assembly and simpler cable management. The connector system offers a hybrid 1.00mm pitch signal and 3.00mm pitch power configuration with an active latching feature.

The connector has nominal current carrying capacity of 10A/pin max. for power and 1.5A/pin max. for signal.

- ComboLock® Hand tool P/N:
 - 10164147-001HT (AWG 24-26-28-30)
 - 10164148-001HT (AWG 18-20)
- Contact (MPNs):
 - 10162696-001LF & 10162696-002LF (Use with 10164147-001HT)
 - 10162697-002LF (Use with 10164148-001HT)
- Ergonomic handle for an optimal grip



Amphenol CS recommends using the hand tool for prototyping and small production quantities. This tool should only be used for the terminals and wire gauges specified in this document. To learn more about how to use our all-in-one Crimping Hand Tool, [click](#) to watch the video.

Hand Tool Assembly


ComboLock® 1.00/3.00mm
P/N : 10164147-001HT & 10164148-001HT



Unlock 2 pins by pushing towards them.



Extract the pins.



Open the handles and insert the tool head into the open holes. The laser marking of both parts should match.



Lock the pins by pushing toward them. Hand Tool is ready to use.



NOTE

Amphenol CS recommends using the hand tool for prototyping and small production quantities only.

Premature Release of the Hand Tool

In case of an assembly mistake / operating fault the pliers can be opened prematurely by unlocking the integrated ratchet by pushing the handles gently together and at the same time releasing the locking lever.

By doing so the handles can be opened completely and the crimp contact can be released.



CAUTION

Do not use the crimped wire in case of a premature release!

Please pay attention that in-correct crimped wires are disposed and not processed.


Professionelles Crimphandwerkzeug Professional crimping hand tool

Verwendungsbereich / Field of application

AWG 24/26/28/30

Amphenol CS PN: 10164147-001HT

- Leichte Handhabung
Easy handling
 - Linearer Hub
Straight action principle
 - Entriegelbare Zwangssperre
Ratchet release
 - Kontaktpositionierung mit Klapppositionierer
Contact positioning with flap locator
 - Präzise gefertigte Profile
Precisely manufactured profiles
 - Oberfläche brüniert
Burnished surface
 - Ergonomisch geformte Soft-Handgriffe Farbe: verkehrsblau (ähnl. RAL 5017) Ergonomically formed soft-grips Colour: traffic blue (similar RAL 5017)
 - RoHS konform
RoHS compliant
- Abmessungen:
Dimensions:
- Länge: ca. 195 mm
Length: approx. 195 mm
 - Breite: ca. 65 mm
Width: approx. 65 mm
 - Tiefe: ca. 29 mm
Depth: approx. 29 mm
 - Gewicht: ca. 300 g
Weight: approx. 300 g



Anwendungsbereich: Application range:

Leiterquerschnitt Cross section range	Leiter wire	Crimphöhe Leiter Crimp height wire ± 0,03	Crimpbreite Leiter Crimp width wire ± 0,04	Crimphöhe Isolation Crimp height insulation ±0,04	Crimpbreite Isolation Crimp width insulation ±0,04	Kontakt Typ: Contact Typ:
AWG 26		0,53	1,10	1,4	1,34	ComboLock WTB
AWG 24		0,58	1,20			
AWG 28		0,53	0,8	1,16	1,26	
AWG 30		0,47		1,12	1,28	

Professionelles Crimphandwerkzeug

Verwendungsbereich / Field of application

AWG 18/20


Amphenol CS PN: 10164148-001HT

- **Leichte Handhabung**
Easy handling
- **Linearer Hub**
Straight action principle
- **Entriegelbare Zwangssperre**
Ratchet release
- **Kontaktpositionierung mit Klapppositionierer**
Contact positioning with flap locator
- **Präzise gefertigte Profile**
Precisely manufactured profiles
- **Oberfläche brüniert**
Burnished surface
- **Ergonomisch geformte Soft-Handgriffe Farbe: verkehrsblau (ähnlt. RAL 5017)** Ergonomically formed soft-grips Colour: traffic blue (similar RAL 5017)
- **RoHS konform**
RoHS compliant

Abmessungen:

Dimensions:

- Länge: ca. 195 mm
Length: approx. 195 mm
- Breite: ca. 65 mm
Width: approx. 65 mm
- Tiefe: ca. 29 mm
Depth: approx. 29 mm
- Gewicht: ca. 300 g
Weight: approx. 300 g



Anwendungsbereich:

Application range:

Leiterquerschnitt Cross section range	Leiter wire	Crimphöhe Leiter Crimp height wire ± 0,03	Crimpbreite Leiter Crimp width wire ± 0,04	Crimphöhe Isolation Crimp height insulation ±0,04	Crimpbreite Isolation Crimp width insulation ±0,04	Kontakt Typ: Contact Typ:
AWG 20		1,23	1,87	2,66	2,42	ComboLock WTE
AWG 18		1,3	2,2	2,78	2,47	