



REV.	DATE	DESCRIPTION
NC	06/01/99	INITIAL RELEASE
A	04/29/07	UPDATE DRAWING FORMAT



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020”	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						04/29/07
6	COVER	BRASS	GOLD	1		CHECKED			PART DESCRIPTION SMA R/A PANEL ADAPTER —				
5	RING	BRASS	GOLD	1		ISSUED							
4	CONTACT PIN	BRASS	GOLD	1		SHEET	1 OF 1		PART NO. 132267				
3	INSULATOR	TEFLON	NATURAL	1	CAD FILE			DWG. NO. 132267.DWG					
2	CONTACT PIN	BER. COPPER	GOLD	1	C:/132/132267.DWG								
1	BODY	BRASS	GOLD	1	DO NOT SCALE DRAWING			REV.	A	SIZE	A	SCALE	NA
DESCRIPTION					MATERIAL	FINISH	QTY						