



CrystalFree™ Industrial Temp Oscillator

Active Oscillators at the price of Passive Crystals

3DN

PRELIMINARY DATA SHEET

Features

- Frequency Range: 4 to 133 MHz
- Output Type: CMOS
- Initial Frequency Tolerance: ± 50 ppm
- Supply Voltage: 1.8 to 3.3 V
- Power Consumption: 1.9 mA (1.8 V)
- Standby Current: < 1 μ A
- Standard Package: 5.0 x 3.2 x 0.85 mm
2.5 x 2.0 x 0.55 mm
- Operating Temperature: -40 to 85 °C



This product is rated "Green", please contact factory for environmental compliancy information

Specification


Parameter	Symbol	Specifications			Conditions
Supply Voltage	VDD	1.8 V ± 10%	2.5 V ± 10%	3.3 V ± 10%	Nominal ± tolerance
Output Frequency	F _{OUT}	4 to 133 MHz			See ordering code
Initial Frequency Tolerance	F _{ITOL}	± 50 ppm			25°C
Supply Current	IDD	1.9 mA	2.0 mA	2.2 mA	Typical; No load condition; 75 MHz
Quiescent Current	I _{STBY}	1 uA			Maximum; STBY# = GND
Input LOW level	V _{IL}	0.3 VDD (max)			At STBY# pin
Input HIGH level	V _{IH}	0.7 VDD (min)			
Output LOW level	V _{OL}	0.1 VDD (max)			I _{OL} = - 1 mA
Output HIGH level	V _{OH}	0.9 VDD (min)			I _{OH} = 1 mA
Tolerance over Temperature	F _{TEM}	± 400 ppm			Over specified operating temperatures
Rise/Fall Time	T _R / T _F	1.6 ns	1.2 ns	1.0 ns	Maximum; 20% to 80% x VDD; Output load (CL) = 4 pF
Symmetry	SYM	45% / 55%			Worst case; For frequencies ≤ 100 MHz;
		40% / 60%			Worst case; For frequencies > 100 MHz;
Start-up time	T _{ST}	400 us			Output valid time after VDD meets the specified range & STBY# transition
Period Jitter	PJ _{RMS}	17 ps	6 ps	5 ps	Output load (CL) = 4 pF; 75 MHz
Cycle to Cycle Jitter	CCJ _{MAX}	120 ps	50 ps	40 ps	Output load (CL) = 4 pF; 75 MHz; measured over 12 K cycles

Note: Above specifications are typical at room temperature (25°C) unless otherwise specified.

* Inclusive of initial frequency accuracy, operating temperature range, supply variation, load variation, 3 times solder reflow, shock, vibration and 10 years aging at 25°C.

Package Outline and Dimensions

Typical PCB Land Pattern



Absolute Maximum Ratings

Stresses beyond those listed under *Absolute Maximum Ratings* may cause permanent damage to the device. These ratings are stress specifications only. Functional operation of product at these or under any condition beyond those listed in the operating specifications is not implied. Exposure to absolute maximum rated conditions may affect product reliability.

Item	Maximum Absolute Rating
VDD	4.6 V
STBY#	-0.5 V to VDD + 0.5 V
OUT	-0.5 V to VDD + 0.5 V
Storage Temperature	-65°C to 150°C


Pin Descriptions

Pin #	Name	Description
1	STBY#	Standby Mode ¹ (0 = Output Disabled)
2	GND	Ground
3	OUT ²	CMOS Output
4	VDD	Power


1. Pulled high internally

2. Weak pull down to GND during STBY# enable and startup


Solder Reflow Profile



Output Waveform



Ordering Information



Package Suffix	Minimum Order Quantity (MOQ)		Factory Order Increment (FOI)	
	T & R	Bulk	T & R	Bulk
NSG	2500	1260 (18 Tubes)	2500	1260 (18 Tubes)
NVG	3000	1250 (Canister)	3000	1250 (Canister)

www.IDT.com

6024 Silver Creek Valley Road
San Jose, California 95138

Sales
800-345-7015 (inside USA)
+1 408-284-8200 (outside USA)
Fax: 408-284-2775

Technical Support
crystalfreetechsupport@idt.com
+1 408-360-5656

DISCLAIMER Integrated Device Technology, Inc. (IDT) and its subsidiaries reserve the right to modify the products and/or specifications described herein at any time and at IDT's sole discretion. All information in this document, including descriptions of product features and performance, is subject to change without notice. Performance specifications and the operating parameters of the described products are determined in the independent state and are not guaranteed to perform the same way when installed in customer products. The information contained herein is provided without representation or warranty of any kind, whether express or implied, including, but not limited to, the suitability of IDT's products for any particular purpose, an implied warranty of merchantability, or non-infringement of the intellectual property rights of others. This document is presented only as a guide and does not convey any license under intellectual property rights of IDT or any third parties.

IDT's products are not intended for use in life support systems or similar devices where the failure or malfunction of an IDT product can be reasonably expected to significantly affect the health or safety of users. Anyone using an IDT product in such a manner does so at their own risk, absent an express, written agreement by IDT.

Integrated Device Technology, IDT and the IDT logo are registered trademarks of IDT. Other trademarks and service marks used herein, including protected names, logos and designs, are the property of IDT or their respective third party owners.

Copyright 2010, 2011. All rights reserved.