Specifications

Photo is representative

Eaton BK/GMC-1.5-R

Eaton GMC Series Medium time-delay fuse 1.50A, 250 Vac, 32 Vdc (self certified), BK-GMC-1-5-R

General specifications	
PRODUCT NAME	Eaton Bussmann series GMC time-delay fuse
CATALOG NUMBER	BK/GMC-1.5-R
UPC	051712642088
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant
PRODUCT TYPE	Time-delay fuse

Powering Business Worldwide

Downloaded from Arrow.com.

Product specifications

USED WITH	out axial leads
AMPERAGE RATING	1.50 A
INTERRUPT RATING	100 AIC at 250 Vac 10 kAIC at 125 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
RESPONSE TIME	60 min at 135%, 2 min at 200%
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	100
VOLTAGE RATING	250 Vac, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - BK/GMC-1.5-R Eaton GMC medium time delay glass tube fuses data sheet

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
DATE:	

Eaton Corporation plc Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

Downloaded from Arrow.com.