




PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-1004	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-1007	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE

SINGLE DRIVER ASSEMBLY OFFSET MOUNT






TABS FOR MOUNTING
DRIVER VERTICAL




TABS FOR MOUNTING
DRIVER HORIZONTAL


ETL LABEL



ISO VIEW








MOUNTING FOR VERTICAL DRIVER
MOUNTING HOLE LOCATION
HOLES FOR A #6-32 SELF TAPPING SCREW



MOUNTING FOR HORIZONTAL DRIVER
MOUNTING HOLE LOCATION
HOLES FOR A #6-32 SELF TAPPING SCREW








- NOTES:
- 1. HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - 2. STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																					
 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC:					<div>molex</div>													
	MM/INCH		NTS																				
 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)									EC NO: 700562 DRWN: UKOWSHIKARAN CHK'D: RCG APPR: RCG 2022/03/22 2022/03/28 2022/03/28					DRIVER ASSEMBLY SINGLE/DUAL CHANNEL								
 = 0		MM		INCH		INITIAL REVISION: DRWN: GALLENO2 APPR: JAGRO 2017/12/12 2018/10/03									DOCUMENT NUMBER 1809960000		DOC TYPE PSD		DOC PART 000		REVISION B		
	4 PLACES	±		±																			
	3 PLACES	±		±																			
	2 PLACES	±	0.25	± 0.01																			
DIVISIONAL SYMBOLS	1 PLACE	±	0.5	± 0.02	THIRD ANGLE PROJECTION					DRAWING A1-SIZE		SERIES 180996		MATERIAL NUMBER SEE TABLE		CUSTOMER GENERAL MARKET		SHEET NUMBER 1 OF 7					
	0 PLACES	±		±																			
	ANGULAR TOL																			± °			
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS																							

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-3104	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-3107	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE

SINGLE DRIVER ASSEMBLY CENTER MOUNT






- NOTES:
- 1. HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 - 2. STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------



FUNCTIONAL SYMBOLS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
<div>E/A = 0</div>		DIMENSION UNITS		SCALE		CURRENT REV DESC:				<div>molex</div>							
		MM/INCH		NTS													
<div>E/C = 0</div>		GENERAL TOLERANCES (UNLESS SPECIFIED)															
				MM	INCH												
<div>E/P = 0</div>		4 PLACES		±						±	EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28				DRIVER ASSEMBLY SINGLE/DUAL CHANNEL		
		3 PLACES		±		±											
DIVISIONAL SYMBOLS		2 PLACES		±	0.25	±	0.01										
		1 PLACE		±	0.5	±	0.02										
		0 PLACES		±		±											
		ANGULAR TOL		±		°											
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A1-SIZE		180996		SEE TABLE		GENERAL MARKET		3 OF 7			
										DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION	
										1809960000		PSD		000		B	

PART NO.	DRIVER ASM	INPUT CURRENT MAX.	OUTPUT CURRENT MAX.	OUTPUT POWER MAX.	STATUS
180996-5101	SINGLE CHANNEL	300mA	350mA	14W	ACTIVE
180996-5102	SINGLE CHANNEL	430mA	500mA	20W	ACTIVE
180996-5103	SINGLE CHANNEL	600mA	700mA	28W	ACTIVE
180996-5104	SINGLE CHANNEL	900mA	1050mA	42W	ACTIVE
180996-5106	SINGLE CHANNEL	750mA	880mA	35W	ACTIVE
180996-5107	SINGLE CHANNEL	260mA	300mA	13W	ACTIVE
180996-5108	SINGLE CHANNEL	1025mA	1200mA	51W	ACTIVE
180996-5109	SINGLE CHANNEL	1200mA	1400mA	59W	ACTIVE

SINGLE DRIVER ASSEMBLY UNIVERSAL MOUNT






TABS FOR MOUNTING
DRIVER VERTICAL








ETL LABEL

TABS FOR MOUNTING
DRIVER HORIZONTAL




ISO VIEW

- NOTES:
1. HOUSING EXTRUSION
MATERIAL: ANODIZED ALUMINUM
 2. STAMPED END CAP LEFT & RIGHT
MATERIAL: ALUMINUM
FINISH: TEXTURED POWDER COAT, BLACK

FUNCTIONAL SYMBOLS <div></div> <div></div> <div></div> <div>DIVISIONAL SYMBOLS</div>	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																				
	DIMENSION UNITS			SCALE			CURRENT REV DESC:						<div>molex</div>								
	MM/INCH			NTS																	
	GENERAL TOLERANCES (UNLESS SPECIFIED)						EC NO: 700562 DRWN: UKOWSHIKARAN CHK'D: RCG APPR: RCG INITIAL REVISION: DRWN: GALLENO2 APPR: JAGRO						DRIVER ASSEMBLY SINGLE/DUAL CHANNEL								
			MM		INCH																
	4 PLACES	±		±																	
	3 PLACES	±		±																	
	2 PLACES	±	0.25	±	0.01																
	1 PLACE	±	0.5	±	0.02																
	0 PLACES	±		±																	
	ANGULAR TOL						±	°	THIRD ANGLE PROJECTION <div></div> <div></div>						DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS						1809960000		PSD							000		B				
						MATERIAL NUMBER		CUSTOMER							SHEET NUMBER						
						A1-SIZE		180996		SEE TABLE		GENERAL MARKET		5 OF 7							


INSERT DRIVER SINGLE OR DUAL) —
INTO BOX (NOTE ORIENTATION
OF TRANSCEND OR CoreSync LOGO)

— MANUFACTURING/WAREHOUSE
LABEL (SEE NOTE 3)



MASTER PACK BOX

DRIVER (SINGLE OR DUAL) BOX-



MANUFACTURING/WAREHOUSE
LABEL (SEE NOTE 3)

NOTES:

1. PLACE DRIVER ASSEMBLY INTO BOX AS SHOWN.
2. PLACE 24 DRIVER BOXES INTO MASTERPACK.
3. INSTRUCTION SHEET CAN BE FOUND AT

DIRECTORY BELOW:

http://www.literature.molex.com/SQLImages/kelmscott/Molex/PDF_Images/987651-6631.pdf

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																	
	DIMENSION UNITS		SCALE		CURRENT REV DESC:					<div>molex</div>								
	MM/INCH		NTS															
	GENERAL TOLERANCES (UNLESS SPECIFIED)									DRIVER ASSEMBLY SINGLE/DUAL CHANNEL								
		MM	INCH															
	$\frac{F}{A} = 0$	4 PLACES		±	±		EC NO: 700562 DRWN: UKOWSHIKARAN 2022/03/22 CHK'D: RCG 2022/03/28 APPR: RCG 2022/03/28					PRODUCT CUSTOMER DRAWING						
	$\frac{F}{C} = 0$	3 PLACES		±	±													
	DIVISIONAL SYMBOLS	2 PLACES		±	0.25	±											0.01	
		1 PLACE		±	0.5	±	0.02											
		0 PLACES		±	±													
ANGULAR TOL		±	°															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS							THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
									A1-SIZE		180996		SEE TABLE		GENERAL MARKET		7 OF 7	

DOCUMENT STATUS	P1	RELEASE DATE	2022/03/28	18:00:12
-----------------	----	--------------	------------	----------