



E32-L25L 2M

Fiber optic sensor head, limited reflective, square, top-view, R10 fiber, 2 m cable

Specifications

Sensing method	Limited reflective
Shape	Square
Product Width (unpacked)	18 mm
Product Depth (unpacked)	4 mm
Product Height (unpacked)	16 mm
Application	Object detection
Temperature range	-40-70 °C
Sensing distance	7 mm
Cable length	2 m
Bending radius	10 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP50
Sensing surface orientation	Top-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV
Smart Fiber Amplifier



E3NX-CA
High-performance color
mark sensor



E3NX-CA
High-performance color
mark sensor



E3NX-MA
Smart Fiber Amplifier Units



E3X-NA
Digital fiber amplifier with
potentiometer adjustment



E3NX-FA
High-performance digital
fiber amplifier

IO-Link

Downloads

CAD Library



Fiber Sensor Selection
Selection Guide

EN PDF 15.9 MB

TERMS OF WEBSITE USE

This PDF document was created from the European OMRON Industrial Automation website on 18 April, 2026. Click here for [terms of use](#).

OMRON

INDUSTRIAL AUTOMATION | INDUSTRIAL.OMRON.EU