



**Part Number :** [1200660579](#)  
**Product Description :** Micro-Change (M12)  
Double-Ended Cordset, 8 Poles, Male  
(Straight) to Female (Straight), 24 AWG, Black  
PUR/PVC Cable, 1.0m (3.28') Length  
**Series Number :** 120066  
**Status :** Active  
**Product Category :** Circular Industrial  
Cordsets  
**Engineering Number :** 888030P02M010




Documents & Resources

Drawings  
[1200660579\\_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead... per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474  
- chemSHERPA (xml)

## EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	Active
Category	Circular Industrial Cordsets
Series	120066
Description	Micro-Change (M12) Double-Ended Cordset, 8 Poles, Male (Straight) to Female (Straight), 24 AWG, Black PUR/PVC Cable, 1.0m (3.28') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	78172553169

#### Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V AC / 36V DC

#### Physical

Cable Diameter	6.70mm (.264")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	None
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass

Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	94.990/g
Orientation	Straight to Straight
Poles	8
Temperature Range - Operating	-30° TO +80°C
Wire/Cable Type	PUR/PVC
Wire Size (AWG)	24

---

This document was generated on Apr 26, 2025