



Pushing Performance

RJ1 10G RJ45 plug Cat6, 8p IDC straight



Image is for illustration purposes only. Please refer to product description.

Part number	09 45 151 1560
Specification	RJ1 10G RJ45 plug Cat6, 8p IDC straight
HARTING eCatalogue	https://b2b.harting.com/09451511560

Identification

Category	Connectors
Series	HARTING RJ Industrial®
Element	Cable connector
Specification	Straight

Version

Termination method	IDC termination
Shielding	Fully shielded, 360° shielding contact
Number of contacts	8

Technical characteristics

Conductor cross-section	0.1 ... 0.32 mm² solid and stranded
Conductor cross-section	AWG 27 ... AWG 22 solid and stranded
Wire outer diameter	≤1.6 mm
Rated current	1.75 A
Rated voltage	50 V AC 60 V DC
Transmission characteristics	Cat. 6 Class E _A up to 500 MHz
Data rate	10 Mbit/s 100 Mbit/s 1 Gbit/s 2.5 Gbit/s 5 Gbit/s 10 Gbit/s
Insulation resistance	> 5 x 10 ⁹ Ω



Pushing Performance

Technical characteristics

Contact resistance	≤20 mΩ
Limiting temperature	-40 ... +70 °C
Insertion force	25 N
Withdrawal force	25 N
Mating cycles	≥750
Degree of protection acc. to IEC 60529	IP20
Cable diameter	4.5 ... 9 mm
Test voltage U _{DC}	1 kV (contact-contact) 1.5 kV (contact-ground)
Vibration resistance	10-500 Hz, 5 g, 0.35 mm, 2h/axis 7.9 m/s ² acc. to IEC 61373 Category 1 Class B
Shock resistance	25 g / 11 ms, 5 shocks / axis and direction acc. to IEC 61373 Category 1 Class B

Material properties

Material (insert)	Thermoplastic resin (PBT)
Colour (insert)	Yellow
Material (contacts)	Copper alloy
Material (hood/housing)	Polyamide (PA)
Colour (hood/housing)	Black
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Potassium 1,1,2,2,3,3,4,4,4-nonafluorobutane-1-sulphonate
ECHA SCIP number	cb23d166-5e46-433f-a5dd-2c5c6285baaa
California Proposition 65 substances	No

Specifications and approvals

Specifications	IEC 60603-7 Mating face IEC 11801 EN 50173-1 EN 45545-2 R26: HL1, HL2, HL3
Approvals	DNV GL



Pushing Performance

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079
	CSA-C22.2 No. 182.3 ECBT8.E102079
PROFINET	Yes

Commercial data

Packaging size	1
Net weight	24 g
Country of origin	Romania
European customs tariff number	85366990
eCl@ss	27440101 Rectangular connectors (set)