

HBL2815 -- Twist-Lock Flanged Inlet



4P5W, 30A 3PH 120/208V AC, L21-30P, White
Nylon

Product Specifications

Product Type



Twist-Lock
Devices

Product Item Flanged Inlet

Wiring Scheme 4-Pole, 5-Wire Grounding

Amperage 30A

Voltage 3 Phase Y 120/208V AC

NEMA Configuration L21-30P

Item Style Standard

Device Color White

Terminal Retainer Material Clear polycarbonate

Blade Material Brass

Terminal Clamp Material .08" (2) steel-nickel plated

Terminal Screw Material #10-32 Brass (white finish on neutral screw when used) Multi-drive

Ground Screw Material #10-32 Brass (green finish) Multi-drive

Body Holding Screw Material Steel, zinc plated Multi-drive

Body Contact Carrier Material Natural White Nylon

Flanged Casing Material Natural White Nylon

Mounting Screw Material Nickel-plated Brass Round head screws

Ratings Molded In or Stamped On

Catalog No Permanently ink marked on product

Dielectric Voltage Withstand 2,000V minimum

Current Interrupting Certified for current interrupting at full rated current

Temperature Rise Max 30C temperature rise at full rated current after 50 cycles of overload at 150% of rated current at a power factor of .75.

Terminal Accommodation 30A #10 AWG

Terminal Identification Terminals identified in accordance with UL 498 (X, Y, Z, White, Green)

Flammability HB or better per UL 94 or CSA 22.2 No. 0.6

Operating Temperatures Maximum Continuous 75 C Minimum -40 C (w/o impact)

Listings FED SPEC UL/CSA

UPC Number 783585039671

Weight in LBs 0.3

Link to Drawing Library [Click here for Library](#)

Link to PDF Catalog [Click here for Catalog](#)



NEMA L21-30P
30A 30Y
120/208V AC
UL/CSA
3 PH

NEMA Configuration

