



HIRSCHMANN

A BELDEN BRAND

Product information N11R EF F


Industrial Connecting Solutions: Circular Connectors: MIL, DIN, Universal Connectors: DIN 43651 Connectors (NR series): Straight cable socket: N11R EF F

<https://catalog.beldensolutions.com:443/link/57078-24228-256281-256284-24367-24368-36228/en/conf/uistate>

Name	N11R EF F
	Straight cable socket, strain relief by means of a clamping cage
Delivery informations	
Availability	available
Product description	
Description	Straight cable socket, strain relief by means of a clamping cage
Type	N11R EF F
Order No.	933 101-100
Type of contact	female
Number of contacts	11 + PE
Cable gland	PG 16
Cable diameter	12 mm to 14 mm
Conductor size	max. 0.5 mm ²
Standard	DIN 43651
Housing Color	black
Technical data	
Pin dimensions	1.6 mm
Rated voltage	AC/DC 60 V
Rated current	5 A
Contact resistance	<= 5 mOhm
Type of termination	crimp
Suitable cables	0.14 mm ² to 0.5 mm ²
Material	
Contact surface material	Ag
Contact bearer material	PET
Housing material	PET
Environmental conditions	
Protection class (IEC 60529)	IP 65
Temperature range	-40 °C to +90 °C
Packing unit	
Packaging unit	10 pieces
Scope of delivery and accessories	
Scope of delivery	1 cable sockets, not assembled, in polythene bag, with assembly instructions
Accessories to order separately	can be plugged into N11R AM, N11R AM 5 contacts: RBC 162

Picture

Drawing



Belden Deutschland GmbH

Im Gewerbepark 2
58579 Schalksmühle
Germany
Phone: +49 7127/14-1806
E-Mail: icos-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.