





T
S
R
Q
P
N
M
L
K
J
H
G
F
E
D
C
B
A

LumaLink CABLE P/N	LENGTH L (ft)	LumaLink CABLE P/N	LENGTH L (ft)
1062837301	5.0 +0.67/-0	1062837343	205.0 +4.1/-0
1062837302	8.0 +0.67/-0	1062837344	210.0 +4.2/-0
1062837303	10.0 +0.67/-0	1062837345	215.0 +4.3/-0
1062837305	15.0 +0.67/-0	1062837346	220.0 +4.4/-0
1062837306	20.0 +0.67/-0	1062837347	225.0 +4.5/-0
1062837307	25.0 +0.67/-0	1062837348	230.0 +4.6/-0
1062837308	30.0 +1.0/-0	1062837349	235.0 +4.7/-0
1062837309	35.0 +1.0/-0	1062837350	240.0 +4.8/-0
1062837310	40.0 +1.0/-0	1062837351	245.0 +4.9/-0
1062837311	45.0 +1.0/-0	1062837352	250.0 +5.0/-0
1062837312	50.0 +1.0/-0	1062837353	255.0 +5.1/-0
1062837313	55.0 +1.0/-0	1062837354	260.0 +5.2/-0
1062837314	60.0 +1.0/-0	1062837355	265.0 +5.3/-0
1062837315	65.0 +1.3/-0	1062837356	270.0 +5.4/-0
1062837316	70.0 +1.4/-0	1062837357	275.0 +5.5/-0
1062837317	75.0 +1.5/-0	1062837358	280.0 +5.6/-0
1062837318	80.0 +1.6/-0	1062837359	285.0 +5.7/-0
1062837319	85.0 +1.7/-0	1062837360	290.0 +5.8/-0
1062837320	90.0 +1.8/-0	1062837361	295.0 +5.9/-0
1062837321	95.0 +1.9/-0	1062837362	300.0 +6.0/-0
1062837322	100.0 +2.0/-0	1062837363	305.0 +6.1/-0
1062837323	105.0 +2.1/-0	1062837364	310.0 +6.2/-0
1062837324	110.0 +2.2/-0	1062837365	315.0 +6.3/-0
1062837325	115.0 +2.3/-0	1062837366	320.0 +6.4/-0
1062837326	120.0 +2.4/-0	1062837367	325.0 +6.5/-0



NOTES:

- CONNECTOR ENDCAPS ARE NOT SHOWN BUT INLCUED.
- MAX. INSERTION LOSS PER CONNECTOR AT 850nm: 0.5dB. CABLE ATTENUATION 3.0 dB/km MAX. IS NOT UNCLUDED. MAX. RETURN LOSS AT 850nm: -20dB.
- OPERATING TEMPERATURE: 0° TO +60°C.
- BOTH PRODUCT LABELS ARE PRINTED WITH MOLEX P/N AND SERIAL NUMBER.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex LUMALINK CABLE ASSEMBLY, MPO(M) TO MPO(F), MM 50/125 OM4, TYPE A							
INCH/MM		1:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 707629 DRWN: IGUMIN CHK'D: GGENCHANOK APPR: GGENCHANOK				PRODUCT CUSTOMER DRAWING							
ANGULAR TOL ± °															
4 PLACES		±		INITIAL REVISION: DRWN: IGUMIN APPR: IGUMIN				DOCUMENT NUMBER 1062837301		DOC TYPE PSD		DOC PART 000		REVISION C	
3 PLACES		±													
2 PLACES		±		2022/05/17 2022/05/25 2022/05/25											
1 PLACE		±													
0 PLACES		±		2018/01/03 2018/05/18											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						E-SIZE		106283		SEE TABLE				1 OF 1	

CONNECTIONS	
FROM	TO
P1-1 THRU P1-12	P2-1 THRU P2-12

DOCUMENT STATUS	P1	RELEASE DATE	2022/05/25	22:53:06
-----------------	----	--------------	------------	----------