




+ HARNESSING
CABLE BRAIDS



✓ Active

TE CONNECTIVITY (TE)
LWB-101-3.0(10)

LWB-101-3.0(10)
TE Internal Number: CQ50583001

EU RoHS Compliant
EU ELV Compliant

Product Type Braid
Plating Tin
Braid Material Copper Alloy
Braid Coverage (%) 90

↓ **PRODUCT DRAWING**
English

DOCUMENTATION

Product Drawings

INSTALITE LIGHTWEIGHT SCREENING BRAID
PDF
English

FEATURES

Please review product documents or [contact us](#) for the latest agency approval information.
Please Note: Use the Product Drawing for all design activity.

Product Type Features
Product Type Braid

Electrical Characteristics

DC Resistance (Nominal) (mΩ) 28

Body Features

Plating Tin
Braid Material Copper Alloy

Dimensions

Cable Entry Diameter 3 – 4.5 mm [.118 – .177 in]
Length (ft) 32.08
Length (m) 10
Weight (Nominal) (kg/km) 8.5

Usage Conditions

Operating Temperature Range (°C) -65 – 150

Packaging Features

Packaging Quantity 10
Packaging Method Reel

Other

Braid Coverage (%) 90

Statement of Compliance

Statement of Compliance
PDF