


Part Number : [2010212024](#)

Product Description : Slim-Grid Header, 24 Circuits, Through Hole, Right-Angle, Shrouded, 0.05µm Gold (Au) Plated, 4.00mm Tail Length, without Peg, Tube, Lead-Free

Series Number : 201021

Status : Obsolete

Product Category : Board-to-Board Connectors



Documents and Resources

[2010212024_stp.zip](#)

[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2009890001-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Board-to-Board Connectors
Series	201021
Description	Slim-Grid Header, 24 Circuits, Through Hole, Right-Angle, Shrouded, 0.05µm Gold (Au) Plated, 4.00mm Tail Length, without Peg, Tube, Lead-Free
Application	Board-to-Board
Comments	4.3 Amps per Pole with only 1 contact powered up; 1.4 Amps per Pole with max contacts powered up
Component Type	Plug
Product Name	Slim-Grid
UPC	889056921114

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	1.4A
Voltage - Maximum	125V AC

Physical

Breakaway	No
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black

Durability (mating cycles max)	500
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.899/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tube
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	3.00mm
PC Tail Length	4.00mm
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.051µm
Plating min - Termination	2.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	WAVE
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Slim-Grid Vertical Receptacles	<u>78120</u>

This document was generated on Aug 10, 2026

Obsolete