




**Part Number :** [530470460](#)

**Product Description :** 1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Gold Flash Plating, Friction Lock, 4 Circuits, Tray, 2.30mm PC Tail Length

**Series Number :** 53047

**Status :** Active

**Product Category :** PCB Headers and Receptacles



---

## Documents and Resources

### Drawings

[530470460 sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[Symbol and Footprint \(Multi-Format\)](#)

[530470460.dxf](#)

### Specifications

[510210000-AS-000.pdf](#)


[SPK-53047-001-001.pdf](#)

[510210006-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44; 33; 34
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)6375-

	DC (05 Nov 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

## Part Details

### General

Status	Active
Category	PCB Headers and Receptacles
Series	53047
Description	1.25mm Pitch, PicoBlade PCB Header, Single Row, Vertical, Through Hole, Gold Flash Plating, Friction Lock, 4 Circuits, Tray, 2.30mm PC Tail Length
Application	Signal, Wire-to-Board
Component Type	PCB Header
Product Name	PicoBlade
UPC	193264603886

### Agency

UL	E29179
----	--------

### Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

Voltage - Maximum	125V
-------------------	------

## Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Mated Height	5.20mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	91.160/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Tray
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	0.80mm
PC Tail Length	2.30mm
Pitch - Mating Interface	1.25mm
Plating min - Termination	1.000µm
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole

---

## Mates With / Use With

## Mates with Part(s)

Description	Part Number
PicoBlade Single Row Receptacle Housings	<u>51021</u>
PicoBlade Female-to-PicoBlade Female Off-the-Shelf (OTS) Cable Assemblies	<u>15134</u>

---

This document was generated on Jan 23, 2026