





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	7/2/15	
A		UPDATED DIM.	2/15/16	HR



RECOMMENDED PCB LAYOUT



Wire Size AWG	Rated Voltage	CIRCUITS			
		2	4~6	8~10	12~24
#18	250V	9 A	8 A	7 A	6 A
#20		7 A	6 A	5 A	5 A
#22		5 A	4 A	4 A	4 A
#24		4 A	3 A	3 A	3 A

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: Natural

Contact: Brass, Sel Gold plated

Electrical:

Voltage rating: 600V AC, DC (R.M.S)

Dielectric withstanding voltage: 1500 VAC for 1 minute

Temperature Rating:

Operating temperature: -40° to +105°C

Environmental:

Lead free, RoHS compliant.



Positions: 2, 4, 6, 8, 10, 12, 14, 16, 18, 20, 22 & 24

A = .165 [4.20] x No. of Spaces + .213 [5.40]

B = .165 [4.20] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES .X ±.10 Ø.X ±.10 .XX ±.020 Ø.XX ±.015 .XXX ±.015 Ø.XXX ±.010				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710		
APPROVALS DRAWN AY 7/2/15 CHECKED LL 7/2/15 APPROVED				TITLE STRAIGHT HOUSING, MALE TERMINAL PCB MOUNT, NO DRAIN HOLES		
SIZE X PART NO. DMF-XX-S-SG-NDH-V0 REF: S00123T				REV. A SCALE: NTS SHEET 1 OF 1		