
Data sheet

# QB 4 WI RA6 IS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

## Product image



The distribution or multiplication of a potential to adjoining terminal blocks is realized via a cross-connection. Additional wiring effort can be easily avoided. Even if the poles are broken out, contact reliability in the terminal blocks is still ensured. Our portfolio offers pluggable and screwable cross-connection systems for modular terminal blocks.

### General ordering data

| | |
|---|---|
| Version | Cross-connector (terminal), when screwed in, grey, 27 A, Number of poles: 4, Pitch in mm (P): 6.00, Insulated: Yes, Width: 3 mm |
| Order No. | 0482900000 |
| Type | QB 4 WI RA6 IS |
| GTIN (EAN) | 4008190086169 |
| Qty. | 50 items |



Downloaded from Arrow.com.

# Data sheet

## QB 4 WI RA6 IS

**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

# Technical data

### Approvals

| | |
|---|---|
| ROHS | Conform |

### Dimensions and weights

| | | | |
|---|---|---|---|
| Depth | 19 mm | Depth (inches) | 0.748 inch |
| Height | 28 mm | Height (inches) | 1.1024 inch |
| Width | 3 mm | Width (inches) | 0.1181 inch |
| Net weight | 1.65 g | | |

### Temperatures

| | | | |
|---|---|---|---|
| Storage temperature | -25 °C...55 °C | Ambient temperature | -50 °C...55 °C |
| Continuous operating temp., min. | -50 °C | Continuous operating temp., max. | 100 °C |

### Environmental Product Compliance

| | |
|---|---|
| RoHS Compliance Status | Compliant without exemption |
| REACH SVHC | No SVHC above 0.1 wt% |

### Material data

| | | | |
|---|---|---|---|
| Basic material | PA 66 | Colour | grey |
| UL 94 flammability rating | V-2 | | |

### System specifications

| | |
|---|---|
| Version | Cross-connector |

### Additional technical data

| | | | |
|---|---|---|---|
| Type of fixing | when screwed in | Installation advice | Direct mounting |
| Explosion-tested version | No | Type of mounting | when screwed in |

### Dimensions

| | |
|---|---|
| Pitch in mm (P) | 6.00 mm |

### General

| | | | |
|---|---|---|---|
| Number of poles | 4 | Installation advice | Direct mounting |

### Rating data

| | | | |
|---|---|---|---|
| Rated voltage | 400 V | Nominal current | 27 A |

### Classifications

| | | | |
|---|---|---|---|
| ETIM 8.0 | EC000489 | ETIM 9.0 | EC000489 |
| ETIM 10.0 | EC000489 | ECLASS 14.0 | 27-25-03-03 |
| ECLASS 15.0 | 27-25-03-03 | | |



Downloaded from Arrow.com.