NVMFD5875NL

MOSFET – Power, Dual N-Channel, Logic Level, Dual SO8FL

60 V, 33 mΩ, 22 A

ON Semiconductor®


www.onsemi.com

Features

- Low $R_{DS(on)}$ to Minimize Conduction Losses
- Low Capacitance to Minimize Driver Losses
- NVMFD5875NLWF – Wettable Flanks Option for Enhanced Optical Inspection
- AEC–Q101 Qualified and PPAP Capable
- These Devices are Pb–Free, Halogen Free and are RoHS Compliant

$V_{(BR)DSS}$	$R_{DS(on)}$ MAX	I_D MAX
60 V	33 mΩ @ 10 V	22 A
	45 mΩ @ 4.5 V	

Dual N–Channel



MAXIMUM RATINGS (T_J = 25°C unless otherwise noted)


Parameter			Symbol	Value	Unit
Drain–to–Source Voltage			V_{DSS}	60	V
Gate–to–Source Voltage			V_{GS}	±20	V
Continuous Drain Current $R_{\theta JC}$ (Notes 1, 2, 3, 4)	Steady State	T_C = 25°C	I_D	22	A
		T_C = 100°C		15	
Power Dissipation $R_{\theta JC}$ (Notes 1, 2, 3)		T_C = 25°C	P_D	32	W
		T_C = 100°C		16	
Continuous Drain Current $R_{\theta JA}$ (Notes 1 & 3, 4)	Steady State	T_A = 25°C	I_D	7	A
		T_A = 100°C		5.8	
Power Dissipation $R_{\theta JA}$ (Notes 1, 3)		T_A = 25°C	P_D	3.2	W
		T_A = 100°C		2.2	
Pulsed Drain Current	T_A = 25°C, t_p = 10 μs		I_{DM}	80	A
Operating Junction and Storage Temperature			T_J, T_{stg}	–55 to +175	°C
Source Current (Body Diode)			I_S	19	A
Single Pulse Drain–to–Source Avalanche Energy (T_J = 25°C, V_{DD} = 24 V, V_{GS} = 10 V, R_G = 25 Ω)	($I_{L(pk)}$ = 14.5 A, L = 0.1 mH)		E_{AS}	10.5	mJ
	($I_{L(pk)}$ = 6.3 A, L = 2 mH)			40	
Lead Temperature for Soldering Purposes (1/8″ from case for 10 s)			T_L	260	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

THERMAL RESISTANCE MAXIMUM RATINGS (Note 1)


Parameter	Symbol	Value	Unit
Junction–to–Case – Steady State (Note 2, 3)	$R_{\theta JC}$	4.65	°C/W
Junction–to–Ambient – Steady State (Note 3)	$R_{\theta JA}$	47	

1. The entire application environment impacts the thermal resistance values shown, they are not constants and are only valid for the particular conditions noted.



DFN8 5x6 (SO8FL) CASE 506BT

MARKING DIAGRAM



5875NL = Specific Device Code for NVMFD5875NL
5875LW = Specific Device Code for NVMFD5875NLWF
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

ORDERING INFORMATION

Device	Package	Shipping†
NVMFD5875NLT1G	DFN8 (Pb–Free)	1500 / Tape & Reel
NVMFD5875NLWFT1G	DFN8 (Pb–Free)	1500 / Tape & Reel
NVMFD5875NLT3G	DFN8 (Pb–Free)	5000 / Tape & Reel
NVMFD5875NLWFT3G	DFN8 (Pb–Free)	5000 / Tape & Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.

© Semiconductor Components Industries, LLC, 2015

Downloaded from Arrow.com.

2. Psi (Ψ) is used as required per JESD51−12 for packages in which substantially less than 100% of the heat flows to single case surface.
3. Surface−mounted on FR4 board using a 650 mm^2, 2 oz. Cu pad.
4. Maximum current for pulses as long as 1 second is higher but is dependent on pulse duration and duty cycle.

Downloaded from Arrow.com.

ELECTRICAL CHARACTERISTICS (T_J = 25°C unless otherwise specified)

Parameter	Symbol	Test Condition		Min	Typ	Max	Unit
OFF CHARACTERISTICS							
Drain−to−Source Breakdown Voltage	$V_{(BR)DSS}$	V_{GS} = 0 V, I_D = 250 μA		60			V
Drain−to−Source Breakdown Voltage Temperature Coefficient	$V_{(BR)DSS}/T_J$				53		mV/°C
Zero Gate Voltage Drain Current	I_{DSS}	V_{GS} = 0 V, V_{DS} = 60 V	T_J = 25°C			1.0	μA
			T_J = 125°C			10	
Gate−to−Source Leakage Current	I_{GSS}	V_{DS} = 0 V, V_{GS} = ±20 V				±100	nA
ON CHARACTERISTICS (Note 5)							
Gate Threshold Voltage	$V_{GS(TH)}$	V_{GS} = V_{DS}, I_D = 250 μA		1.0		3.0	V
Negative Threshold Temperature Coefficient	$V_{GS(TH)}/T_J$				3.5		mV/°C
Drain−to−Source On Resistance	$R_{DS(on)}$	V_{GS} = 10 V	I_D = 7.5 A		27	33	mΩ
		V_{GS} = 4.5 V	I_D = 7.5 A		37	45	
Forward Transconductance	g_{FS}	V_{DS} = 15 V, I_D = 5.0 A			7.0		S
CHARGES AND CAPACITANCES							
Input Capacitance	C_{iss}	V_{GS} = 0 V, f = 1.0 MHz, V_{DS} = 25 V			540		pF
Output Capacitance	C_{oss}				55		
Reverse Transfer Capacitance	C_{rss}				36		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 4.5 V, V_{DS} = 48 V, I_D = 5.0 A			5.9		nC
Threshold Gate Charge	$Q_{G(TH)}$				0.62		
Gate−to−Source Charge	Q_{GS}				1.64		
Gate−to−Drain Charge	Q_{GD}				2.80		
Total Gate Charge	$Q_{G(TOT)}$	V_{GS} = 10 V, V_{DS} = 48V, I_D = 5.0A			11	20	nC
SWITCHING CHARACTERISTICS (Note 6)							
Turn−On Delay Time	$t_{d(on)}$	V_{GS} = 4.5 V, V_{DS} = 48 V, I_D = 5.0 A, R_G = 2.5 Ω			8.1		ns
Rise Time	t_r				15.8		
Turn−Off Delay Time	$t_{d(off)}$				11.8		
Fall Time	t_f				3.9		
Turn−On Delay Time	$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 48 V, I_D = 5.0 A, R_G = 2.5 Ω			4.9		ns
Rise Time	t_r				6.4		
Turn−Off Delay Time	$t_{d(off)}$				14.5		
Fall Time	t_f				2.4		
DRAIN−SOURCE DIODE CHARACTERISTICS							
Forward Diode Voltage	V_{SD}	V_{GS} = 0 V, I_S = 5.0 A	T_J = 25°C		0.8	1.2	V
			T_J = 125°C		0.7		
Reverse Recovery Time	t_{RR}	V_{GS} = 0 V, d_{IS}/d_t = 100 A/μs, I_S = 5.0 A			14.5		ns
Charge Time	t_a				11.5		
Discharge Time	t_b				3.1		
Reverse Recovery Charge	Q_{RR}				11		nC
PACKAGE PARASITIC VALUES							
Source Inductance	L_S	T_A = 25°C			0.93		nH
Drain Inductance	L_D				0.005		
Gate Inductance	L_G				1.84		
Gate Resistance	R_G				1.5		Ω

5. Pulse Test: pulse width = 300 μs, duty cycle ≤ 2%.
6. Switching characteristics are independent of operating junction temperatures.

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 1. On−Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. On−Resistance vs. Gate−to−Source Voltage




Figure 4. On−Resistance vs. Drain Current and Gate Voltage




Figure 5. On−Resistance Variation with Temperature




Figure 6. Drain−to−Source Leakage Current vs. Voltage

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS




Figure 7. Capacitance Variation




Figure 8. Gate−to−Source vs. Gate Charge




Figure 9. Resistive Switching Time Variation vs. Gate Resistance




Figure 10. Diode Forward Voltage




Figure 11. Maximum Rated Forward Biased Safe Operating Area

Downloaded from Arrow.com.

TYPICAL CHARACTERISTICS





Figure 12. Thermal Response

Downloaded from Arrow.com.


DFN8 5x6, 1.27P Dual Flag (SO8FL−Dual)


CASE 506BT
ISSUE F


DATE 23 NOV 2021



SCALE 2:1









DETAIL B
ALTERNATE
CONSTRUCTION

NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.30 MM FROM THE TERMINAL TIP.
4. PROFILE TOLERANCE APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.
5. DIMENSIONS D1 AND E1 DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
6. SEATING PLANE IS DEFINED BY THE TERMINALS. A1 IS DEFINED AS THE DISTANCE FROM THE SEATING PLANE TO THE LOWEST POINT ON THE PACKAGE BODY.
7. A VISUAL INDICATOR FOR PIN 1 MUST BE LOCATED IN THIS AREA.

	MILLIMETERS		
DIM	MIN	NOM	MAX
A	0.90	–––	1.10
A1	–––	–––	0.05
b	0.33	0.42	0.51
b1	0.33	0.42	0.51
c	0.20	–––	0.33
D		5.15 BSC	
D1	4.70	4.90	5.10
D2	3.90	4.10	4.30
D3	1.50	1.70	1.90
E		6.15 BSC	
E1	5.70	5.90	6.10
E2	3.90	4.15	4.40
e		1.27 BSC	
G	0.45	0.55	0.65
h	–––	–––	12 °
K	0.51	–––	–––
K1	0.56	–––	–––
L	0.48	0.61	0.71
M	3.25	3.50	3.75
N	1.80	2.00	2.20




SOLDERING FOOTPRINT*



DIMENSION: MILLIMETERS

*For additional information on our Pb−Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

GENERIC MARKING DIAGRAM*



XXXXXX = Specific Device Code
A = Assembly Location
Y = Year
W = Work Week
ZZ = Lot Traceability

*This information is generic. Please refer to device data sheet for actual part marking. Pb−Free indicator, “G” or microdot “▪”, may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON50417E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped “CONTROLLED COPY” in red.
DESCRIPTION:	DFN8 5X6, 1.27P DUAL FLAG (SO8FL−DUAL)	PAGE 1 OF 1

onsemi and onsemi are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

Downloaded from Arrow.com.

onsemi, ONSEMI , and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent−Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as−is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:
Technical Library: www.onsemi.com/design/resources/technical−documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support
For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales

◊

Downloaded from Arrow.com.