

## 1-1825136-7 Product Details

[+ Share](#) [Print](#) [Email](#)



1-1825136-7

TE Internal Number: 1-1825136-7

 Active

### Toggle Switches

 [Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

#### Product Highlights:

- A Series
- Single Pole - Double Throw Configuration (Pole-Throw)
- Current Rating = 0.4 VA A
- Mount Style = Through-Hole
- Termination Type = Vertical Right Angle

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)  [Request Sample](#)  [Find Similar Products](#)  [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [GEMINI A SERIES TOGGLE SWITCH, SINGLE POLE, 2 POSITION](#) (PDF, English)

#### Catalog Pages/Data Sheets:

- [SWITCHES CORE PROGRAM CATALOG](#) (PDF, English)
- [GEMINI SERIES SWITCHES QUICK REF GUIDE 2-1773458-5](#) (PDF, English)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Additional Product Images:

- [Product Photo](#)

#### Related Products:

- [Tooling](#)

[List all Documents](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Series = A
- Configuration (Pole-Throw) = Single Pole - Double Throw
- Termination Type = Vertical Right Angle

#### Electrical Characteristics:

- Current Rating (A) = 0.4 VA

#### Termination Features:

- Seal Type = Terminal Seal (epoxy)

#### Body Features:

- Mount Style = Through-Hole

#### Contact Features:

- Contact Plating = Gold

#### Housing Features:

- Toggle Actuation = Vertical
- Toggle Style = Baton Short
- Toggle Length (mm [in]) = 6.86 [0.270]
- Process Sealed = No
- Bushing Style = Unthreaded
- Bushing Type = Plain

#### Configuration Features:

- [Operating Function](#) = On On

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

#### Other:

- Brand = Alcoswitch

### Corporate Information

[Who We Are](#)

[Investors](#)

[News Room](#)

[Supplier Portal](#)

[Careers](#)

### Quick Links

[Check Distributor Inventory](#)

[Cross Reference](#)

[Find Documents & Drawings](#)

[Product Compliance Support Center](#)

[Site Map](#)

### Customer Support

[Email or Chat With Us](#)

[Find a Phone Number](#)

[Search Knowledge Base](#)

[Manage your Account](#)

### Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address



Provide Website Feedback