


High Voltage MLC Chips

FLEXITERM® - 600V to 5000V Applications



High value, low leakage and small size are difficult parameters to obtain in capacitors for high voltage systems. AVX special high voltage MLC chips capacitors meet these performance characteristics and are designed for applications such as snubbers in high frequency power converters, resonators in SMPS, and high voltage coupling/DC blocking. These high voltage chip designs exhibit low ESRs at high frequencies.

To make high voltage chips, larger physical sizes than are normally encountered are necessary. These larger sizes require that special precautions be taken in applying these chips in surface mount assemblies. In response to this, and to follow from the success of the FLEXITERM® range of low voltage parts, AVX is delighted to offer a FLEXITERM® high voltage range of capacitors, FLEXITERM®.


The FLEXITERM® layer is designed to enhance the mechanical flexure and temperature cycling performance of a standard ceramic capacitor, giving customers a solution where board flexure or temperature cycle damage are concerns.

HOW TO ORDER

1808	A	C	272	K	A	Z	1	A
AVX Style	Voltage	Temperature Coefficient	Capacitance Code (2 significant digits + no. of zeros)	Capacitance Tolerance	Test Level	Termination*	Packaging	Special Code
0805	600V/630V = C	C0G = A	Examples:	C0G: J = ±5%		Z = FLEXITERM®	2 = 7" Reel	A = Standard
1206	1000V = A	X7R = C	10 pF = 100	K = ±10%		100% Tin	4 = 13" Reel	
1210	1500V = S		100 pF = 101	M = ±20%		(RoHS Compliant)		
1808	2000V = G		1,000 pF = 102	X7R: K = ±10%				
1812	2500V = W		22,000 pF = 223	M = ±20%				
1825	3000V = H		220,000 pF = 224	Z = +80%, -20%				
2220	4000V = J		1 µF = 105					
2225	5000V = K							

Notes: Capacitors with X7R dielectrics are not intended for applications across AC supply mains or AC line filtering with polarity reversal. Contact plant for recommendations. Contact factory for availability of Termination and Tolerance options for Specific Part Numbers.

*** AVX offers nonstandard chip sizes. Contact factory for details.



DIMENSIONS

MILLIMETERS (INCHES)

SIZE	0805	1206	1210*	1808*	1812*	1825*	2220*	2225*
(L) Length	2.10 ± 0.20 (0.083 ± 0.008)	3.30 ± 0.30 (0.130 ± 0.012)	3.30 ± 0.40 (0.130 ± 0.016)	4.60 ± 0.50 (0.181 ± 0.020)	4.60 ± 0.50 (0.181 ± 0.020)	4.60 ± 0.50 (0.181 ± 0.020)	5.70 ± 0.50 (0.224 ± 0.020)	5.70 ± 0.50 (0.224 ± 0.020)
(W) Width	1.25 ± 0.20 (0.049 ± 0.008)	1.60 ^{+0.30} _{-0.10} (0.063 ^{+0.012} _{-0.004})	2.50 ± 0.30 (0.098 ± 0.012)	2.00 ± 0.20 (0.079 ± 0.008)	3.20 ± 0.30 (0.126 ± 0.012)	6.30 ± 0.40 (0.248 ± 0.016)	5.00 ± 0.40 (0.197 ± 0.016)	6.30 ± 0.40 (0.248 ± 0.016)
(T) Thickness Max.	1.35 (0.053)	1.80 (0.071)	2.80 (0.110)	2.20 (0.087)	2.80 (0.110)	3.40 (0.134)	3.40 (0.134)	3.40 (0.134)
(t) terminal min. max.	0.50 ± 0.20 (0.020 ± 0.008)	0.60 ± 0.20 (0.024 ± 0.008)	0.75 ± 0.35 (0.030 ± 0.014)	0.75 ± 0.35 (0.030 ± 0.014)	0.75 ± 0.35 (0.030 ± 0.014)	0.75 ± 0.35 (0.030 ± 0.014)	0.85 ± 0.35 (0.033 ± 0.014)	0.85 ± 0.35 (0.033 ± 0.014)

*Reflow Soldering Only



Performance of SMPS capacitors can be simulated by downloading SpiCalci software program - <http://www.avx.com/SpiApps/default.asp#spicalci>

Custom values, ratings and configurations are also available.

High Voltage MLC Chips

FLEXITERM® - 600V to 5000V Applications



NP0 (C0G) Dielectric

Performance Characteristics

Capacitance Range	10 pF to 0.100 µF (+25°C, 1.0 ±0.2 Vrms, 1kHz)
Capacitance Tolerances	±5%, ±10%, ±20%
Dissipation Factor	0.1% max. (+25°C, 1.0 ±0.2 Vrms, 1kHz)
Operating Temperature Range	-55°C to +125°C
Temperature Characteristic	0 ±30 ppm/°C (0 VDC)
Voltage Ratings	600, 630, 1000, 1500, 2000, 2500, 3000, 4000 & 5000 VDC (+125°C)
Insulation Resistance (+25°C, at 500 VDC)	100K MΩ min. or 1000 MΩ - µF min., whichever is less
Insulation Resistance (+125°C, at 500 VDC)	10K MΩ min. or 100 MΩ - µF min., whichever is less
Dielectric Strength	Minimum 120% rated voltage for 5 seconds at 50 mA max. current

NP0 (C0G) CAPACITANCE RANGE

PREFERRED SIZES ARE SHADED

Case Size	0805			1206					1210					1808							1812								
Soldering	Reflow/Wave			Reflow/Wave					Reflow Only					Reflow Only							Reflow Only								
(L) Length	2.10 ± 0.20 (0.083 ± 0.008)			3.30 ± 0.30 (0.130 ± 0.012)					3.30 ± 0.40 (0.130 ± 0.016)					4.60 ± 0.50 (0.181 ± 0.020)							4.60 ± 0.50 (0.181 ± 0.020)								
(W) Width	1.25 ± 0.20 (0.049 ± 0.008)			1.60 ± 0.30/-0.10 (0.063 ± 0.012/-0.004)					2.50 ± 0.30 (0.098 ± 0.012)					2.00 ± 0.20 (0.079 ± 0.008)							3.20 ± 0.30 (0.126 ± 0.012)								
(T) Thickness	1.35 (0.053)			1.80 (0.071)					2.80 (0.110)					2.20 (0.087)							2.80 (0.110)								
(t) Terminal	0.50 ± 0.20 (0.020 ± 0.008)			0.60 ± 0.20 (0.024 ± 0.008)					0.75 ± 0.35 (0.030 ± 0.014)					0.75 ± 0.35 (0.030 ± 0.014)							0.75 ± 0.35 (0.030 ± 0.014)								
Voltage (V)	600	630	1000	600	630	1000	1500	2000	600	630	1000	1500	2000	600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000
Cap (pF)	1.5	1R5	A	A		X	X	X	X	X																			
	1.8	1R8	A	A		X	X	X	X	X																			
	2.2	2R2	A	A		X	X	X	X	X																			
	2.7	2R7	A	A		X	X	X	X	X																			
	3.3	3R3	A	A		X	X	X	X	X																			
	3.9	3R9	A	A		X	X	X	X	X																			
	4.7	4R7	A	A		X	X	X	X	X																			
	5.6	5R6	A	A		X	X	X	X	X																			
	6.8	6R8	A	A		X	X	X	X	X																			
	8.2	8R2	A	A		X	X	X	X	X																			
	10	100	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	12	120	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	15	150	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	18	180	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	22	220	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	27	270	A	A	A	X	X	X	X	X	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	33	330	A	A	A	X	X	X	D	D	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	39	390	A	A	A	X	X	X	D	D	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	47	470	A	A	A	X	X	M	D	D	C	C	D	D	D	C	C	C	C	C	C	C	C	C	C	C	C	C	E
	56	560	A	A	A	X	X	M	C	C	C	C	D	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	F
	68	680	A	A	A	X	X	M	C	C	C	C	D	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	F
	82	820	X	X	X	X	X	C	C	C	C	C	D	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	F
	100	101	X	X	X	X	X	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	F
	120	121	C	C	C	X	X	C	E	E	E	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	C	F
	150	151	C	C	C	X	X	C	E	E	E	C	C	C	E	E	C	C	C	F	F	F	F	F	F	F	F	F	G
	180	181	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	C	F	F	F	F	F	F	F	F	F	G
	220	221	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	C	F	F	F	F	F	F	F	F	F	G
	270	271	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	C	F	F	F	F	F	F	F	F	F	G
	330	331	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	390	391	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	470	471	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	560	561	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	680	681	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	750	751	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	820	821	C	C	C	X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	1000	102				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	1200	122				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	1500	152				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	1800	182				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	2200	222				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	2700	272				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	3300	332				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	3900	392				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	4700	472				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	5600	562				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	6800	682				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
	8200	822				X	X	E	E	E	E	C	C	E	E	E	C	C	F	F	F	F	F	F	F	F	F	F	G
Cap (µF)	0.010	103																											
	0.012	123																											
	0.015	153																											
	0.018	183																											
	0.022	223																											
	0.033	333																											
	0.047	473																											
	0.056	563																											
	0.068	683																											
	0.100	104																											
Voltage (V)	600	630	1000	600	630	1000	1500	2000	600	630	1000	1500	2000	600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000
Case Size	0805			1206					1210					1808							1812								



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

High Voltage MLC Chips

FLEXITERM® - 600V to 5000V Applications



NP0 (C0G) CAPACITANCE RANGE

PREFERRED SIZES ARE SHADED

Case Size		1825								2220								2225									
Soldering		Reflow Only								Reflow Only								Reflow Only									
(L) Length	mm	4.60 ± 0.50								5.70 ± 0.50								5.72 ± 0.25									
	(in.)	(0.181 ± 0.020)								(0.224 ± 0.020)								(0.225 ± 0.010)									
(W) Width	mm	6.30 ± 0.40								5.00 ± 0.40								6.35 ± 0.25									
	(in.)	(0.248 ± 0.016)								(0.197 ± 0.016)								(0.250 ± 0.010)									
(T) Thickness	mm	3.40								3.40								3.40									
	(in.)	(0.134)								(0.134)								(0.134)									
(t) Terminal	mm	0.75 ± 0.35								0.85 ± 0.35								0.85 ± 0.35									
	max	(0.030 ± 0.014)								(0.033 ± 0.014)																	
Voltage (V)		600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000
Cap (pF)	1.5 1R5																										
	1.8 1R8																										
	2.2 2R2																										
	2.7 2R7																										
	3.3 3R3																										
	3.9 3R9																										
	4.7 4R7																										
	5.6 5R6																										
	6.8 6R8																										
	8.2 8R2																										
10 100	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
12 120	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
15 150	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
18 180	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
22 220	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
27 270	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
33 330	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
39 390	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	F	
47 470	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	G	
56 560	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	G	
68 680	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	G	
82 820	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	F	G	
100 101	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	G	G	
120 121	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	G	G	
150 151	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	E	E	E	E	E	E	E	G	G	
180 181	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	F	F	E	E	E	E	E	E	G	G	
220 221	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	F	F	E	E	E	E	E	E	G	G	
270 271	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E			E	E	E	E	E	E	G	G	
330 331	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E			E	E	E	E	E	E	G		
390 391	E	E	E	E	E	E	E	E		E	E	E	E	E	E	E			E	E	E	E	E	E	G		
470 471	E	E	E	E	E	E	E	E		E	E	E	E	E	E	E			E	E	E	E	E	E	G		
560 561	E	E	E	E	E	E	E	E		E	E	E	E	E	E	E			E	E	E	E	E	E	G		
680 681	E	E	E	E	E	F	F			E	E	E	E	F	F				E	E	E	E	E	E			
750 751	E	E	E	E	E	F	F			E	E	E	E	F	F				E	E	E	E	E	E			
820 821	E	E	E	E	E	F	F			E	E	E	E	E	F	F				E	E	E	E	F	E		
1000 102	E	E	E	E	E	F	F			E	E	E	E	E	F	F				E	E	E	E	E	E		
1200 122	E	E	E	E	E	G	G			E	E	E	E	E	G	G				E	E	E	E	F	F		
1500 152	E	E	E	F	F	G	G			E	E	E	F	F	G	G				E	E	E	E	F	F		
1800 182	E	E	E	F	F	G	G			E	E	E	F	F	G	G				E	E	E	E	G	G		
2200 222	E	E	E	G	G					E	E	E	G	G						E	E	E	E				
2700 272	E	E	E	G	G					E	E	E	G	G						E	E	E	F	F			
3300 332	E	E	E	G	G					E	E	E	G	G						E	E	E	F	F			
3900 392	E	E	E	G	G					E	E	E	G	G						E	E	E	G	G			
4700 472	E	E	E	G	G					E	E	E	G	G						F	F	F	G	G			
5600 562	F	F	F	G	G					F	F	F								F	F	F	G	G			
6800 682	F	F	F							F	F	F								F	F	F	G	G			
8200 822	G	G	G							G	G	G								G	G	G					
Cap (µF)	0.010 103																			G	G	G					
	0.012 123																			G	G	G					
	0.015 153																			G	G	G					
	0.018 183																			G	G	G					
	0.022 223																			G	G	G					
	0.033 333																			G	G	G					
	0.047 473																			G	G	G					
	0.056 563																			G	G	G					
	0.068 683																			G	G	G					
	0.100 104																			G	G						
Voltage (V)		600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000
Case Size		1825								2220								2225									

Letter	A	C	E	F	G	X
Max.	0.813	1.448	1.803	2.210	2.794	0.940
Thickness	(0.032)	(0.057)	(0.071)	(0.087)	(0.110)	(0.037)

NOTE: Contact factory for non-specified capacitance



High Voltage MLC Chips

FLEXITERM® - 600V to 5000V Applications



X7R Dielectric

Performance Characteristics

Capacitance Range	10 pF to 0.82 µF (25°C, 1.0 ±0.2 Vrms at 1kHz)
Capacitance Tolerances	±10%; ±20%; +80%, -20%
Dissipation Factor	2.5% max. (+25°C, 1.0 ±0.2 Vrms, 1kHz)
Operating Temperature Range	-55°C to +125°C
Temperature Characteristic	±15% (0 VDC)
Voltage Ratings	600, 630, 1000, 1500, 2000, 2500, 3000, 4000 & 5000 VDC (+125°C)
Insulation Resistance (+25°C, at 500 VDC)	100K MΩ min. or 1000 MΩ - µF min., whichever is less
Insulation Resistance (+125°C, at 500 VDC)	10K MΩ min. or 100 MΩ - µF min., whichever is less
Dielectric Strength	Minimum 120% rated voltage for 5 seconds at 50 mA max. current

X7R CAPACITANCE RANGE

PREFERRED SIZES ARE SHADED

Case Size	0805						1206						1210						1808						1812					
Soldering	Reflow/Wave						Reflow/Wave						Reflow Only						Reflow Only						Reflow Only					
(L) Length	2.10 0.20 (0.083 ± 0.008)						3.30 ± 0.30 (0.130 ± 0.012)						3.30 0.40 (0.130 0.016)						4.60 ± 0.50 (0.181 ± 0.020)						4.60 ± 0.50 (0.181 ± 0.020)					
(W) Width	1.25 0.20 (0.049 ± 0.008)						1.60 +0.30/-0.10 (0.063 +0.012/-0.004)						2.50 0.30 (0.098 0.012)						2.00 0.20 (0.079 ± 0.008)						3.20 ± 0.30 (0.126 ± 0.012)					
(T) Thickness	1.35 (0.053)						1.80 (0.071)						2.80 (0.110)						2.20 (0.087)						2.80 (0.110)					
(t) Terminal	0.50 ± 0.20 (0.020 ± 0.008)						0.60 ± 0.20 (0.024 ± 0.008)						0.75 0.35 (0.030 ± 0.014)						0.75 ± 0.35 (0.030 ± 0.014)						0.75 ± 0.35 (0.030 ± 0.014)					
Voltage (V)	600	630	1000	600	630	1000	1500	2000	600	630	1000	1500	2000	600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	
Cap (pF)	100	101	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	120	121	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	150	151	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	180	181	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	220	221	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	270	271	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	330	331	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	390	391	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	470	471	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	560	561	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	680	681	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	750	751	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	820	821	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	1000	102	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	1200	122	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	1500	152	X	X	C	C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	1800	182	X	X		C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	2200	222	X	X		C	C	E	E	E	E	E	E	E	E	E	E	E	E	E	F	E	E	E	E	E	E	E	E	
	2700	272	X	X		C	C	E	E					E	E	E	F	E	E	E	F	F					E	E	E	
	3300	332	X	X		C	C	E						E	E	E	F	E	E	E	F	F					E	E	E	
	3900	392	X	X		C	C	E						E	E	E	G										E	E	E	
	4700	472	X	X		C	C	E						E	E	E	G										E	E	E	
	5600	562	X	X		C	C	E						E	E	E	G										E	E	E	
	6800	682	X	X		C	C	E						E	E	E											E	E	E	
	8200	822	X	X		C	C	E						E	E	E											E	E	E	
Cap (µF)	0.010	103	C	C		C	C	E						E	E	E											E	E	E	
	0.015	153	C	C		E	E	E						E	E	E											E	E	F	
	0.018	183	C	C		E	E							E	E	E											E	E	G	
	0.022	223	C	C		E	E							E	E	E											E	E	G	
	0.027	273				E	E							E	E												E	E	G	
	0.033	333				E	E							E	E												E	E	G	
	0.039	393												E	E												E	E	G	
	0.047	473												E	E												E	E	G	
	0.056	563												F	F												F	F		
	0.068	683												F	F												F	F		
	0.082	823												F	F												F	F		
	0.100	104												F	F												F	F		
	0.150	154																									G	G		
	0.220	224																									G	G		
	0.270	274																												
	0.330	334																												
	0.390	394																												
	0.470	474																												
	0.560	564																												
	0.680	684																												
	0.820	824																												
	1.000	105																												
Voltage (V)	600	630	1000	600	630	1000	1500	2000	600	630	1000	1500	2000	600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	
Case Size	0805						1206						1210						1808						1812					



The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

High Voltage MLC Chips

FLEXITERM® - 600V to 5000V Applications



X7R CAPACITANCE RANGE

PREFERRED SIZES ARE SHADED

Case Size		1825								2220								2225								3640										
Soldering		Reflow Only								Reflow Only								Reflow Only								Reflow Only										
(L) Length	mm (in.)	4.60 0.50 (0.181 0.020)								5.70 0.50 (0.224 0.020)								5.72 ± 0.25 (0.225 ± 0.010)								9.14 ± 0.25 (0.360 ± 0.010)										
(W) Width	mm (in.)	6.30 0.40 (0.248 ± 0.016)								5.00 0.40 (0.197 0.016)								6.35 ± 0.25 (0.250 ± 0.010)								5.72 ± 0.25 (0.225 ± 0.010)										
(T) Thickness	mm (in.)	3.40 (0.134)								3.40 (0.134)								2.54 (0.100)								2.54 (0.100)										
(t) Terminal	mm max	0.75 0.35 (0.030 ± 0.014)								0.85 0.35 (0.033 ± 0.014)								0.85 ± 0.35 (0.033 ± 0.014)								0.76 (0.030) 1.52 (0.062)										
Voltage (V)		600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000
Cap (pF)	100	101																																		
	120	121																																		
	150	151																																		
	180	181																																		
	220	221																																		
	270	271																																		
	330	331																																		
	390	391																																		
	470	471																																		
	560	561																																		
	680	681																																		
	750	751																																		
	820	821																																		
	1000	102	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	1200	122	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	1500	152	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	1800	182	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	2200	222	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	2700	272	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	3300	332	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	3900	392	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	4700	472	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	5600	562	F	F	F	F	F	F	F		F	F	F	F	F	F	G		F	F	F	F	F	F	F			G	G	G	G	G	G	G	G	
	6800	682	F	F	F	G	G	G	G		F	F	F	F	F	G	G		F	F	F	F	F	G	G			G	G	G	G	G	G	G	G	
	8200	822	F	F	F	G	G	G	G		F	F	F	G	G	G	G		F	F	F	F	F	G	G			G	G	G	G	G	G	G	G	
Cap (µF)	0.010	103	F	F	F	G	G	G	G		F	F	F	G	G	G	G		F	F	F	F	F	G	G			G	G	G	G	G	G	G	G	
	0.015	153	F	F	F	G	G	G		F	F	F	G	G	G				F	F	F	G	G	G	G			G	G	G	G	G	G	G	G	
	0.018	183	F	F	F	G	G			F	F	F	G	G		G			F	F	F	G	G	G			G	G	G	G	G	G	G	G	G	
	0.022	223	F	F	F	G	G			F	F	F	G	G					F	F	F	G	G	G			G	G	G	G	G	G				
	0.027	273	F	F	F	G				F	F	F	G		G				F	F	F	G	G				G	G	G	G	G	G				
	0.033	333	F	F	F	G				F	F	F	G						F	F	F	G		G			G	G	G	G						
	0.039	393	F	F	F	G				F	F	F	G						F	F	F	G					G	G	G	G						
	0.047	473	F	F	F	P				F	F	F	G						F	F	F	G					G	G	G	G						
	0.056	563	F	F	F	G				F	F	F	G						F	F	F	G					G	G	G	G						
	0.068	683	F	F	G					F	F	G							F	F	G						G	G	G	G						
	0.082	823	F	F	G					F	F	G							F	F	G						G	G								
	0.100	104	F	F	G					F	F	G							F	F	G						G	G								
	0.150	154	F	F						F	F	G							F	F	G						G	G								
	0.220	224	F	F						F	F	G							F	F							G	G								
	0.270	274	F	F						F	F								F	F							G	G								
	0.330	334	F	F						F	F								F	F							G	G								
	0.390	394	F	F						F	F								F	F							G	G								
	0.470	474	F	F						F	F								F	F							G	G								
	0.560	564	G	G						G	G								F	F							G	G								
	0.680	684								G	G								G	G																
	0.820	824								G	G								G	G																
	1.000	105								G	G								G	G																
Voltage (V)		600	630	1000	1500	2000	2500	3000	4000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000	600	630	1000	1500	2000	2500	3000	4000	5000
Case Size		1825								2220								2225								3640										

Letter	A	C	E	F	G	P	X
Max. Thickness	0.813 (0.032)	1.448 (0.057)	1.8034 (0.071)	2.2098 (0.087)	2.794 (0.110)	3.048 (0.120)	0.940 (0.037)

NOTE: Contact factory for non-specified capacitance values