

## 5-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch with PoE+, 75W

MODEL NUMBER: NG5POE



Energy-efficient switch provides Gigabit network connection for multiple devices. Recommended for small offices, workgroups, creative workspaces and security applications using IP cameras and other PoE-compatible devices.

### Description

The NG5POE 5-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch adds a Gigabit Ethernet connection with PoE+ capacity to your small office, workgroup or creative workspace.

Especially recommended for security applications to power IP cameras, VoIP phones and other PoE-compatible devices, this energy-efficient switch provides PoE+ compatibility with wireless access points and other devices. Four ports support up to 26W each with a total PoE budget of 75W. Sharing large bandwidth-intensive files, such as CAD drawings and high-definition videos, at Gigabit speeds improves efficiency and cuts costly downtime. IEEE 802.3x flow control allows smooth transmission.

This unmanaged switch features five twisted-pair RJ45 Gigabit Ethernet ports that support auto-negotiable 10/100/1000 Mbps and auto MDI/MDIX cross-over detection. It's plug-and-play with no configuration required and can be up and running immediately. Easy-to-read LEDs indicate power, connection, activity and PoE status for each port.

The NG5POE supports IEEE 802.3az Energy Efficient Ethernet standards by putting unused ports into a low-power state without interrupting network connections. The detachable five-foot power cord with NEMA 5-15P plug connects to any compatible AC source. The heavy-duty metal housing is designed for desktop installation or mounting into 1U of an EIA-standard 19-inch rack with the included brackets.

### Features

#### Highlights

- 5 auto-negotiable 10/100/1000 Mbps RJ45 ports
- 4 ports support 26W PoE+ each; 75W total PoE budget
- Supports auto MDI/MDIX cross-over function
- 2 Gbps switching capacity per port with full duplex
- Plug-and-play with no configuration required

#### Package Includes

- NG5POE 5-Port 10/100/1000 Mbps 1U Rack-Mount/Desktop Gigabit Ethernet Unmanaged Switch
- Detachable AC power cord with NEMA 5-15P plug, 5 ft.
- (2) Mounting brackets
- (8) Screws
- (4) Rubber feet
- Owner's manual



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

#### Unmanaged Network Switch for Home/Small Offices, Workgroups and Security Applications

- 5 twisted-pair RJ45 Gigabit Ethernet ports
- Auto-negotiable 10/100/1000 Mbps
- Automatic MDI/MDIX cross-over detection
- 10 Gbps switching capacity (2 Gbps per port with full duplex)
- LEDs indicate power, connection, activity and PoE status per port
- Supports 9k jumbo frames, MAC address auto-learning and auto-aging, and 802.3x flow control (full duplex) and back pressure (half duplex)

#### 75W Total PoE+ Budget

- 4 ports support up to 26W PoE+ each
- Each port supplies PoE+ power to connected devices via network cable

#### Complies with IEEE 802.3az Energy Efficient Ethernet Standards

- Automatically shifts unused ports to low-power state without interrupting network connection
- Also meets IEEE 802.3ab, 802.3i, 802.3u and 802.3 standards

#### Heavy-Duty Metal Housing

- No-fan design for silent operation
- Detachable 5 ft. AC power cord with NEMA 5-15P plug
- Plug-and-play with no configuration required

#### Versatile Installation Options

- Includes rubber feet for secure placement on flat desktop surface
- Mounts in 1U of EIA-standard 19 in. rack with included brackets
- Grounding lug included

## Specifications

| OVERVIEW                          |                                                                                               |
|-----------------------------------|-----------------------------------------------------------------------------------------------|
| UPC Code                          | 037332194794                                                                                  |
| INPUT                             |                                                                                               |
| Electrical Consumption            | 78W maximum power consumption (at 100% switching capacity and 75W continuous POE consumption) |
| Nominal Input Voltage Description | 100-240V AC nominal input                                                                     |
| Plug Type                         | Detachable NEMA 5-15P input cord                                                              |
| Input Frequency                   | 50/60 Hz                                                                                      |
| Input Cord Length (ft.)           | 5                                                                                             |
| Input Cord Length (m)             | 1.52                                                                                          |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

| USER INTERFACE, ALERTS & CONTROLS |                                                                                                                                                                                                                                                                                                                                                                       |
|-----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| LED Indicators                    | Power LED (Green for Power On); PORTS 1-4 include two LEDs per port (UPPER LED: Green indicates 10/100Mbps link; Amber indicates 1000Mbps link; LEDs flash to indicate port activity / LOWER LED: Green indicates POE is active); PORT 5 includes one LED only (Green indicates 10/100Mbps link; Amber indicates 1000Mbps link; LEDs flash to indicate port activity) |
| PHYSICAL                          |                                                                                                                                                                                                                                                                                                                                                                       |
| Color                             | Black                                                                                                                                                                                                                                                                                                                                                                 |
| Form Factors Supported            | Desktop, Rackmount                                                                                                                                                                                                                                                                                                                                                    |
| Primary Form Factor               | Desktop; Rackmount                                                                                                                                                                                                                                                                                                                                                    |
| Rack Height                       | 1U                                                                                                                                                                                                                                                                                                                                                                    |
| Shipping Dimensions (hwd / cm)    | 7.62 x 24.64 x 43.94                                                                                                                                                                                                                                                                                                                                                  |
| Shipping Dimensions (hwd / in.)   | 3.00 x 9.70 x 17.30                                                                                                                                                                                                                                                                                                                                                   |
| Shipping Weight (kg)              | 2.13                                                                                                                                                                                                                                                                                                                                                                  |
| Shipping Weight (lbs.)            | 4.70                                                                                                                                                                                                                                                                                                                                                                  |
| Unit Dimensions (hwd / cm)        | 4.44 x 27.99 x 17.88                                                                                                                                                                                                                                                                                                                                                  |
| Unit Dimensions (hwd / in.)       | 1.75 x 11.02 x 7.04                                                                                                                                                                                                                                                                                                                                                   |
| Unit Weight (kg)                  | 1.43                                                                                                                                                                                                                                                                                                                                                                  |
| Unit Weight (lbs.)                | 3.15                                                                                                                                                                                                                                                                                                                                                                  |
| ENVIRONMENTAL                     |                                                                                                                                                                                                                                                                                                                                                                       |
| Storage Temperature Range         | -40 to 158F (-40 to 70C)                                                                                                                                                                                                                                                                                                                                              |
| Relative Humidity                 | 10 to 90% (non-condensing)                                                                                                                                                                                                                                                                                                                                            |
| Operating Temperature             | 32 to 104F (0 to 40C)                                                                                                                                                                                                                                                                                                                                                 |
| CONNECTIONS                       |                                                                                                                                                                                                                                                                                                                                                                       |
| Network Switch Ports              | (5) 10/100/1000 (RJ45)                                                                                                                                                                                                                                                                                                                                                |
| PoE Supported Ports               | 4                                                                                                                                                                                                                                                                                                                                                                     |
| PoE Capability                    | 30W (802.3at)                                                                                                                                                                                                                                                                                                                                                         |
| PoE Power Budget (Watts)          | 75                                                                                                                                                                                                                                                                                                                                                                    |
| SPECIAL FEATURES                  |                                                                                                                                                                                                                                                                                                                                                                       |
| Grounding Lug                     | Includes back panel grounding lug                                                                                                                                                                                                                                                                                                                                     |
| STANDARDS & COMPLIANCE            |                                                                                                                                                                                                                                                                                                                                                                       |
| Certifications                    | Compliant Standards: IEEE 802.3ab (1000BASE-T GIGABIT ETHERNET), IEEE 802.3i (10BASE-T ETHERNET), IEEE 802.3u (100BASE-T ETHERNET), IEEE 802.3x (FULL DUPLEX/FLOW CONTROL), IEEE 802.3 (NWAY AUTO-NEGOTIATION), 802.3az (ENERGY EFFICIENT ETHERNET), 802.3at (POE+)                                                                                                   |
| Approvals                         | Tested to UL60950-1: 2007 (2ND ED) +A1+A2 R14 (USA), CAN/CSA C22.2 NO. 60950-1-07, 2ND EDITION, 2014-10 (Canada), NOM (Mexico), FCC CLASS B (Emissions)                                                                                                                                                                                                               |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

| WARRANTY                            |                         |
|-------------------------------------|-------------------------|
| Product Warranty Period (Worldwide) | 5-year limited warranty |

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>