Part Number : 1200688194
Product Description : Micro-Change (M12) In-Line Splitter with Knurled Hexnuts, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), WSOR Cable, 1.0m Length
Series Number : 120009
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 884A30B30M010



Documents and Resources

Drawings

1200688194_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	120009
Description	Micro-Change (M12) In-Line Splitter with Knurled Hexnuts, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), WSOR Cable, 1.0m Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Splitter - In-line
UPC	889056131094

Agency

UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Physical

Color - Cable Jacket	Black
Drop Connector	Micro-Change (M12)
Drop Gender	Male
Keyway	Single

Downloaded from Arrow.com.

LED Indicator	None
Left Trunk Connector	Micro-Change (M12)
Left Trunk Gender	Female
Leg 1 Length	1.0m
Leg 2 Length	1.0m
Material - Cable Jacket	TPU
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Net Weight	18.417/g
Poles	3 Female/4 Male
Right Trunk Connector	Micro-Change (M12)
Right Trunk Gender	Female
Temperature Range - Operating	-25° to +80°C

Downloaded from Arrow.com.