

Part Number : [1300680104](#)

Product Description : BradPower D-Size (1 3/8"-M35) 3-Pole Trunk Tee, with 3-Pole BradPower D-Size (1 3/8"-M35) Drop, Red

Series Number : 130068

Status : Active

Product Category : Industrial Tees and Splitters

Engineering Part Number : TC30C30-200E




Documents and Resources

Drawings

[1300680104 sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

CE - Declaration of Conformity

UKCA - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130068
Description	BradPower D-Size (1 3/8"-M35) 3-Pole Trunk Tee, with 3-Pole BradPower D-Size (1 3/8"-M35) Drop, Red
IP Rating	IP67
Product Name	BradPower D-Size
Type	Power Tap Tee
UPC	78172545166

Agency

UL	E258922
----	---------

Electrical

Current - Maximum per Contact	32.0A
Voltage - Maximum	600V AC/DC

Physical

Drop Connector	BradPower D-Size (1 3/8"-M35)
Drop Gender	Female
Keyway	Single
LED Indicator	None
Left Trunk Connector	BradPower D-Size (1 3/8"-M35)
Left Trunk Gender	Female

Leg 1 Length	N/A
Leg 2 Length	N/A
Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Anodized Aluminum
Net Weight	286.670/g
Poles	3
Right Trunk Connector	BradPower D-Size (1 3/8"-M35)
Right Trunk Gender	Male
Temperature Range - Operating	-20° to +90°C

This document was generated on Jun 09, 2026