Product data sheet

Specifications



Discontinued

APC Smart-UPS, Line Interactive, 3kVA, Tower, 120V, 8x NEMA 5-15R+1x NEMA 5-20R outlets, SmartSlot, AVR, LCD

SMT3000

Discontinued on: Aug 6, 2026

To be end-of-service on: Jun 30, 2030

Overview

Presentation	Intelligent and efficient network power protection from entry level to scalable runtime. Ideal UPS for servers, point-of-sale, routers, switches, hubs and other network devices.

Main

Main input voltage	120 V AC 1 phase
Input connection	NEMA L5-30P
Efficiency at full load	75...154 V adjustable 82...144 V
Input frequency	50/60 Hz +/- 3 Hz auto-sensing
Output voltage	120 V AC 1 phase
Rated power in W	2700 W
Rated power in VA	2880 VA
Output connection	8 NEMA 5-15R 2 NEMA 5-20R
Harmonic distortion	Less than 5 %
Maximum configurable power in VA	2880 VA
Maximum configurable power in W	2700 W
Transfer time	4 ms typical : 8 ms maximum
UPS topology	Line interactive
Waveform type	Sine wave
Output frequency	50/60 Hz +/- 3 Hz sync to mains
Replacement battery	RBC55

Graphs

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph

Complementary

Battery type	Lead-acid internal included
Control panel	Multifunction LCD status and control console

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Downloaded from Arrow.com.

Emergency power off	Yes
Free slot	1
Alarm	Alarm when on battery : distinctive low battery alarm : configurable delays
UPS connectivity	Serial port USB port Available expansion slot
Surge energy rating	530 J
Noise filtering	Full time multi-pole noise filtering : 0.3% IEEE surge let-through : zero clamping response time : meets UL 1449
Cable length	1.8 m
Number of cables	1
Color	Black
Height	432 mm
Width	196 mm
Depth	544 mm
Product weight	52.73 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable
Two post mountable	0
USB compatible	Yes
Mounting mode	Tower
Provided equipment	CD with software Documentation CD Smart UPS signalling RS-232 cable USB cable
Number of power modules	0
Number of power module filled slots	0
Number of power module free slots	0
Redundant	No
Range of product	Smart-UPS
Product or component type	Uninterruptible power supply (UPS)

Environment

Product certification	CSA
Equipment protection policy	Lifetime : $150000
Ambient air temperature for operation	0…40 °C
Ambient air temperature for storage	-15…45 °C
Storage altitude	0…15240 m
Relative humidity	0…95 %
Storage relative humidity	0…95 %
Acoustic level	45 dBA
Heat dissipation	275 Btu/h

Downloaded from Arrow.com.

Operating altitude	0...10000 ft

Batteries & Runtime

Battery type	Lead-acid battery
Extendable runtime	0
Included battery module	0
Empty battery slot	0
Typical recharge time	3 h
RBC quantity	1
Battery life	3…5 year(s)
Battery charging power	247 W rated

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	55.9 cm
Package 1 Width	76.2 cm
Package 1 Length	38.1 cm
Package 1 Weight	60.91 kg
SCC14	731304268703

Contractual warranty

Warranty (in months)	24 Battery|36 UPS

Downloaded from Arrow.com.

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant By Exemption
REACh Regulation	Reference contains Substances of Very High Concern above the threshold
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Use Longer

Lifetime extension

Repair	No

Use Again

Repack and remanufacture

End of life manual availability	End of Life Information
Take-back	No
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Downloaded from Arrow.com.

Image of product / Alternate images

Alternative



Downloaded from Arrow.com.