

Part number

CCFA 0.3



Female crimp contact, CC series, 16 A, turned silver plated, wire cross section 0,14 - 0,37 mm², AWG 26 - 22

Product description

Product type	Crimp contact
Series	CC
Gender	Female

Technical data

Current	16 A
Wire cross-section	0,14 mm ² - 0,37 mm ²
AWG size	26 - 22
Contact type	Turned silver plated

Further technical details

Weight	1,60 g
Operating temperature range (min, max)	-40°C ... +125°C
Conductors stripping length	7,5 mm

Material properties

Main material	Copper alloy
RoHs conformity	Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight
China RoHs - EFUP	50
REACH SVHC substances	Yes Lead
SCIP number	C0979fba-9907-458f-a94a-db781440f273

Approvals / Standards

Certifications	CSA, EAC
UL	ECBT2

General ordering information

EAN13 code	8015747170970
eCl@ss 8.1	27440204
ETIM 7.0	EC000796

Packaging Information

Packaging length	112,00 mm
Packaging height	95,00 mm
Packaging width	117,00 mm
Packaging weight	1,48 kg
Packaging volume	1,24 dm ³
Packaging description	Carton box
Packaging quantity	800 Pcs
Packaging EAN code	8015747171045
Sub-packaging length	50,00 mm
Sub-packaging height	44,00 mm
Sub-packaging width	50,00 mm
Sub-packaging weight	0,19 kg
Sub-packaging volume	0,11 dm ³
Sub-packaging description	Plastic box
Sub-packaging quantity	100 Pcs
Sub-packaging EAN barcode	8015747171052

Part number



CCFA 0.3

Catalogue drawings



Notes

Dimensions shown in mm are not binding and may be changed without notice.

