



Part Number : 1121115001

Series Number : 112111

Product Category : Industrial Ethernet Switches

Product Description : IP67 Unmanaged Ethernet Switch, 5-Port, 10/100 Mb/s Data Speed, 5-pole M12 Ultra-Lock

Status : Active

Engineering Number : DRL-750

Documents & Resources

Drawings

Drawing 1121115001_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2022)4187-DC (10 June 2022)
EU RoHS	Compliant with Exemption 7(c)-I per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Industrial Ethernet Switches
Series	112111
Description	IP67 Unmanaged Ethernet Switch, 5-Port, 10/100 Mb/s Data Speed, 5-pole M12 Ultra-Lock
Approvals	CE certified, UL
Comments	2.0W (24VDC)
IP Rating	IP67
Product Family	Industrial Ethernet Switches
Product Name	IP67 Unmanaged Ethernet Switch
Protocol	EtherNet (IEEE 802.3)
Switch Functionality	Unmanaged
UPC	883906689483

Electrical

Data Speed	Fast Ethernet (10/100Mbps)
EMC	EN 61000-4-2, EN 61000-4-4, EN 61000-4-5, EN 61326
Supply Voltage	24V DC

Physical

Ethernet Connector	M12 D-Coded
Housing Depth	34.00mm
Housing Length	176.00mm
Housing Width	30.00mm
MAC Address	2048
Mechanical Shock	50G (IEC 68-2-29)
Mounting Style	N/A
Net Weight	0.220/kg
Packaging Type	Carton
Ports	5
Power Input	24V DC
Temperature Range - Operating	-40° to +75°C

Uplink Connection	N/A
Vibration	7g (IEC 68-2-29)

This document was generated on Jun 05, 2024