



PCB LAYOUT



SIGN	DATE	DESCRIPTION	APPROVER
△	2009.09.07	The design is changed	Jacke
△	2009.09.07	The electrical is changed	Jacke
△	2010.03.31	Add the 2p mark	Jacke
△	2014.09.27	The current rating is changed from 20A to 10A	Evan

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Materials

- Item① Terminal body:Thermoplastic (UL94V-0)
- Item② Terminal Cover:Thermoplastic (UL94V-0)
- Item③ Female contact:PhBz(CuSn), Tin plated

Electrical

- Voltage rating: 300VAC
- Current rating: 10A
- Withstanding Voltage: 1.6kv
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: us

No. OF POLES	Color	G
02 2 plocs	0 Black (RAL9005)	G RoHS compliant (lead<4%)
03 3 plocs	2 Red (RAL3001/D)	In copper Alloy
...	3 Orange(RAL2011/P)	0000: "@" Logo (Standard)
16 16 plocs	4 Yellow(RAL1018/A)	000A: "ANYTEK" Mark
	5 Green(RAL6018/T)	Any special item by customer request.
	6 Blue (RAL5015/A)	please contact sales department.
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	V7 7.62 W/O flange Series Right-angle (2P~16P)				
PART NO.	V7xx01x1xxxxG			DWG NO.	8V70502
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	
		Evan 2014.09.27	Evan 2014.09.27		Tolerance
				UNIT: mm	X. ±0.5
				SCALE: 1/4	X.X ±0.3
				SHEET: 01/01	X.XX ±0.1
				REV.: E	X° ±1°

POLE	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16
B	7.62	15.24	22.86	30.48	38.1	45.72	53.34	60.96	68.58	76.2	83.82	91.44	99.06	106.68	114.3
A	13.34	20.96	28.58	36.2	43.82	51.44	59.06	66.68	74.3	81.92	89.54	97.16	104.78	112.4	120.02
Tol.	±0.15					±0.20					±0.30				