



TAOGLAS®



Datasheet

24 x 13 mm Miniature Speaker - 8 Ohm

Part No:
SPKM.2413.8.A

Description:

24 x 13mm Miniature Speaker - 8 Ohm 500mW RMS

Compact design for integration in a wide range of products

Features:

8 Ohm Impedance

Rated Input Power 500mW RMS

Max Input Power 800mW peak

High Sensitivity

Dimensions: 24 x 13 x 8.5mm

Connector: Wire Lead

RoHS & Reach Compliant

| | | |
|-------|--------------------------------|----|
| 1. | Introduction | 3 |
| 2. | Specifications | 4 |
| 3. | Speaker Measurement Conditions | 6 |
| 4. | Speaker Characteristics | 7 |
| 5. | Mechanical Drawing | 8 |
| 6. | Packaging | 9 |
| <hr/> | | |
| | Changelog | 10 |

Taoglas makes no warranties based on the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and product descriptions at any time without notice. Taoglas reserves all rights to this document and the information contained herein. Reproduction, use or disclosure to third parties without express permission is strictly prohibited.

Copyright © Taoglas Ltd.



1. Introduction



Featuring a compact design, enabling ease of integration in a wide range of electronics products, including IoT devices, with high levels of long-term reliability and best in class performance Taoglas products are known for.

Our 24 x 13mm Miniature Speaker offers a frequency response of 100 Hz - 10 kHz and high sensitivity, with 8 Ohm impedance and power handling of 0.5W RMS and 0.8W peak. Proven performance in demanding applications where the accurate reproduction of voice communications is required. Taoglas added miniature speakers to our product portfolio to provide both reliable connectivity and high-quality audio solutions from one trusted company.

Please contact your regional Taoglas customer support team for more information or installation guidelines.

The table below shows a guide to help select the best speaker for your application based on size requirements:

| Part Number | Dimensions |
|---------------|------------------|
| SPKM.10.8.A | Ø10 x 3.5 mm |
| SPKM.15.8.A | Ø15 x 3.7 mm |
| SPKM.17.8.A | Ø17 x 4.4 mm |
| SPKM.20.8.A | Ø20 x 4.3 mm |
| SPKM.23.8.A | Ø23 x 6 mm |
| SPKM.28.8.A | Ø28 x 5.1 mm |
| SPKM.2030.8.A | 30 x 20 x 5.1 mm |
| SPKM.2413.8.A | 24 x 13 x 8.7 mm |
| SPKM.289.8.A | 28 x 9 x 3.8 mm |
| SPKM.50.8.A | Ø50 x 8.3 mm |

2. Specifications

| Electroacoustic | |
|----------------------|--|
| Sound Pressure Level | 88 dB SPL (± 3 dB) @1000Hz (0 dB SPL = 20 μ Pa) Measuring Condition: 0.5W (Sine wave) @ 0.1m with baffle |
| Impedance | 8 Ω ($\pm 20\%$) @ 2 kHz with 1 V input signal and without baffle in place |
| Frequency Response | 100 Hz - 10 kHz |
| Resonant Frequency | 1000 Hz ($\pm 20\%$) Typical frequency @ 1 V |
| Nominal Input Power | 500 milliwatts |
| Maximum Input Power | 800 milliwatts |
| Distortion | Less than 15% @ 1KHz , with input levels up to 2.37 V RMS |
| Mechanical | |
| Height | 8.5 mm |
| Length | 28 mm |
| Width | 9 mm |
| Weight | 0.007 Kg |
| Connector | Wire leads – 32 AWG (UL1571) |
| Material | PEI diaphragm with Neodymium Magnet, (without enclosure) |
| Environmental | |
| Temperature Range | -40°C to 80°C |
| Humidity | Non-condensing up to 95% Relative Humidity @ up to 65°C |

| Reliability Testing | | |
|------------------------|--|---------------------|
| High Temperature Test | High Temp | +80°C (±2°C) |
| | Duration | 96 Hours |
| Low Temperature Test | Low Temp | -40°C (±2°C) |
| | Duration | 96 Hours |
| Heat Shock Test | High Temp | +75°C (±2°C) |
| | Low Temp | -40°C (±2°C) |
| | Changeover time | <30 Seconds |
| | Duration | 1 Hour |
| | Cycle | 100 Cycles |
| Humidity Test | Temp | +40°C (±2°C) |
| | Relative humidity | 90 ~ 95% |
| | Duration | 96 Hours |
| Temperature Cycle Test | Temp | -40°C to +75°C |
| | Duration | 45 minutes |
| | Temperature gradient | 1°C to 3°C / minute |
| | Cycle | 25 cycles |
| Drop Test | Mounted with dummy set mass | 100 g |
| | Height | 1 m |
| | Cycle | 6 cycles |
| Load Test | White noise (EIA filter) for 96 hours @ 0.65W (2.37 V) input power | |
| | White noise (EIA filter) for 1 minute @ 0.93W (2.83 V) input power | |


* SPL (Sound Pressure Level) as specified did not deviate more than ±3 dB from initial value, with no significant damage after testing.

3. Speaker Measurement Conditions

3.1 Conditions

| Standard Test Fixture Conditions | |
|----------------------------------|-------------|
| Input Power | 0.5W(2V) |
| Mode | TSR |
| Potentiometer Range | 50dB |
| Sweep Time | 0.5 seconds |


3.2 Measurement Fixture Diagram




4. Speaker Characteristics

4.1 SPL

dB SPL vs. Frequency




5. Mechanical Drawing (Units: mm)




| | Name | Material | Finish | QTY |
|---|------------------------------|-----------|------------------------------|-----|
| 1 | 24x13x8.4mm Frame | ABS+Fe | Black+Zinc Plated-Blue White | 1 |
| 2 | 11.2x7.2x1.2mm 8Ω Voice coil | Cu | Natural | 1 |
| 3 | 10.5x6.5x0.9mm Magnet | Nd-Fe-B | Zinc Plated | 1 |
| 4 | 14.2x9.2mm Diaphragm | PEN | Natural | 1 |
| 5 | Gasket | T=1mm(Fe) | Zinc Plated-Blue White | 1 |
| 6 | UL1571 32AWG Lead wire | PVC | Black | 1 |
| 7 | UL1571 32AWG Lead wire | PVC | Red | 1 |

6. Packaging


1 pcs SPKM.2413.8.A per Blister
Dimensions – 95 x 42 x 17mm



160 pcs SPKM.2413.8.A per EPE Tray
6 Trays SPKM.2413.8.A per Carton
7 pcs SPKM.2413.8.A per Layer Board



960 pcs SPKM.2413.8.A per Carton
Dimensions – 560 x 450 x 330mm



Changelog for the datasheet

SPE-22-8-003 – SPKM.2413.8.A

Revision: D

| | |
|------------------|--|
| Date: | 18-11-2022 |
| Changes: | Mechanical Drawings Updated to Rev D02 |
| Changes Made by: | Carlos Gomes |

Previous Revisions

Revision: A

| | |
|------------------|-------------|
| Date: | 18-02-2022 |
| Changes: | |
| Changes Made by: | Jack Conroy |

Revision: B

| | |
|------------------|--|
| Date: | 17-05-2022 |
| Changes: | Electroacoustic and Mechanical Specs Updated |
| Changes Made by: | Paul Doyle |

Revision: C

| | |
|------------------|--|
| Date: | 15-08-2022 |
| Changes: | Cover updated Introduction updated Specifications updated Reliability test updated Speaker measurement conditions updated |
| Changes Made by: | Carlos Gomes |



www.taoglas.com

