




Agency Approvals:  

RoHS Compliant



Dim ^P	2	3	4	5	6	7	8	9	10	11	12
L	19.5	31.5	43.5	55.5	67.5	79.5	91.5	103.5	115.5	127.5	139.5
TOL ($\pm$)	0.08	0.12	0.16	0.20	0.24	0.28	0.32	0.36	0.40	0.44	0.48

THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF ON-SHORE TECHNOLOGY, INC. AND SHALL NOT BE REPRODUCED, COPIED OR USED IN ANY MANNER WITHOUT THE PRIOR WRITTEN CONSENT OF ON-SHORE TECHNOLOGY, INC.



TITLE		ES1200 Series - 12.0mm Euro Strip, Wire guard, flat base					
PART NO.		ES1200/XXDSFB (xx - number of poles per row)		DWG NO.		ES1200/XXDSFB.DWG	
APPROVED		CHECKED	DESIGNED	DRAWN	5020		Tolerance
KSZ		KSZ	KSZ	KSZ	 UNIT: mm SCALE: NONE		X ±0.15 XX ±0.075 XXX ±0.05
2007.08.01		2007.08.01	2007.08.01	2007.08.01	SHEET: 01/01 REV: A		