

## Protect It! 6-Outlet Surge Protector, 6 ft. (1.8 m) Cord, 2420 Joules

MODEL NUMBER: TR-6



### Highlights

- 6 outlets/6 ft. (1.8 m) cord
- 2420 joule rating

### Package Includes

- TR-6 Surge Suppressor
- Child safety covers
- Color-coded cord identifiers
- Instruction manual and warranty information

### Description

The TR-6 Surge Suppressor has six outlets and a six-foot (1.8-meter) cord with a space-saving right-angle plug. The unit has 2420 joules of surge energy absorption to handle the strongest surges. Diagnostic LEDs alert the user to potential power problems. The TR-6 comes with child safety covers and color-coded cord identifiers.

### Features

- 6 outlets with child safety covers
- 6 ft. (1.8 m) cord with space-saving right-angle plug
- Surge energy absorption: 2420 joules; 78,500 amps
- 15-amp circuit breaker
- 3 diagnostic LEDs indicate AC present, line fault & protection present
- EMI/RFI noise filtering
- Logical outlet spacing accommodates transformers without blocking remaining outlets
- Keyhole supports for wall mounting
- Recessed and lighted power switch
- Color-coded cord identifiers
- \$50,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only) covers connected equipment
- Automatic shutoff permanently cuts power to outlets if protection circuit is incapacitated, preventing equipment damage and indicating replacement is required

### Specifications

OVERVIEW	
UPC Code	037332010315
INPUT	



Powering Business Worldwide

TRIPP LITE  
SERIES

Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Cord Gauge Type	14 gauge; SJT
Input Cord Gauge (AWG)	14
Voltage Compatibility (VAC)	120
Maximum Surge Amps	97000
Input Plug Type	NEMA 5-15P
Input Cord Details	SJT
Input Cord Length (ft.)	6
Right-Angle Plug	Yes
Input Cord Length (m)	1.83
Integrated Cord Clip	No
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Transformer Accommodation	(3) Yes
Right-Angle Outlets	No
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Diagnostic LED(s)	Yes
Switches	Two position red illuminated on/off power switch
Diagnostic LED Details	PROTECTION PRESENT (green), LINE FAULT (red) and LINE OK (green)
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2420
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression
AC Suppression Surge Current Rating	78,500 amps
UL1449 Let Through Rating	400V
EMI / RFI Filtering	Yes
Immunity	Conforms to IEE 587 / ANSI C62.41
Automatic Shut-Off	Yes
<b>DATALINE SURGE SUPPRESSION</b>	



Powering Business Worldwide

TRIPP LITE  
SERIES

Cable (Coax) Protection	No
Network (Ethernet) Protection	No
Telephone/DSL Protection	No
<b>PHYSICAL</b>	
Material of Construction	Plastic
Power Cord Color	Light Gray
Housing Color	Light Gray
Mounting Holes or Slots	Yes
Slot or Hole Mount Measurement (Center to Center)	88.8 mm
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 44.20mm; Distance between vertical outlets = 39mm
Receptacle Color	Light gray
Shipping Dimensions (hwd / in.)	12.00 x 2.40 x 6.10
Shipping Dimensions (hwd / cm)	30.48 x 6.10 x 15.49
Shipping Weight (lbs.)	1.80
Shipping Weight (kg)	0.82
Unit Dimensions (hwd / in.)	1.750 x 3.500 x 9.500
Unit Dimensions (hwd / cm)	4.45 x 8.9 x 24.13
Unit Weight (lbs.)	1.6
Unit Weight (kg)	0.73
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	32° to 104°F (0° to 40°C)
Storage Temperature Range	14° to 122°F (-10° to 50°C)
Operating Humidity Range	10% to 90% RH
Storage Humidity Range	5% to 95% RH
<b>FEATURES &amp; SPECIFICATIONS</b>	
Rotatable Outlets	No
Antimicrobial	No
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Certifications	UL 1449
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty



*Powering Business Worldwide*

TRIPP LITE  
SERIES

Connected Equipment Insurance  
(U.S., Canada & Puerto Rico)

\$50,000 <a class="insuranceLink" href="//tripplite.eaton.com/support/insurance-policy">Ultimate Lifetime  
Insurance</a> 

1000 Eaton Boulevard

Cleveland, OH 44122

United States

<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.