







N=Number of contacts
Dim.L=Nx5.08
Dim.B=(N-1)x5.08

Poles Dim.	2-8P	9-15P	16-24P
Dim.B	±0.20	±0.25	±0.30
Dim.L	±0.20	±0.30	±0.40



P.C.B LAYOUT

- Material:
- Item 1 Terminal housing : Thermoplastic (UL 94V-0)
 - Item 2 Clamp : Brass ,Ni plated
 - Item 3 Wire guard solder pin : Brass ,Tin plated
 - Item 4 Terminal screw: Steel Zinc plating"- "slot type

- Electrical UL
- Voltage rating: 300VAC
 - Current rating: 10A
 - Wire range:
 - Solid wire(AWG): 16-26
 - Stranded wire(AWG): 16-26
 - Torque(Lb-In): 3.5
 - Screw: M3.0
 - Wire strip length: 6-7mm
 - Withstanding Voltage: 16KV
 - Operating temperature: -40°C to +115°C
 - Soldering temperature: 250°C±10°C/5 Sec
 - Safety Approval: 

△ YC XX 21 x 0 XXXX G

- | | | | |
|----------------|---------|---------------------------|-----------------------|
| 02 2 CONTACTS | 0 Black | 0000:"@ "Logo (Standard) | Pb < 40,000ppm (RoHS) |
| 03 3 CONTACTS | 5 Green | 000A:"ANYTEK"Logo | |
| | 6 Blue | Any special item by | |
| 24 24 CONTACTS | 8 Grey | customer request, | |
| | | please contact sales | |
| | | department. | |

SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part NO is Changed	Tason
△	01/08/09	Temperature changed from -30°C~+105°C to -40°C~+115°C	Kind
△	01/08/09	Terminal screw changed from M2.5 to M3.0	Kind
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YC 5.08 Series 2P-24P		
PART NO.	YCxx21x0xxxxG		
APPROVED	CHECKED	DESIGNED	DRAWN
		Kind 2009.01.08	Kind 2009.01.08
		CUST NO.	DWG NO.
			8YC0001
		UNIT: mm	Tolerance
		SCALE: NONE	X. ±0.50
		REV.: G	X.X ±0.30
		SHEET: 01/01	X.XX ±0.10
			X° ±1°