

7.4kW Single-Phase 230V Basic PDU, 4 C19 Outlets, IEC 309 32A Blue Input, 3.6 m Cord, 1U Rack-Mount

MODEL NUMBER: **PDUH32HV19**



Delivers 230V single-phase AC power to multiple loads from a utility outlet, generator or UPS system in a high-density IT environment. Ideal for data centers, server rooms and network wiring closets.

Description

The PDUH32HV19 7.4kW Single-Phase 230V Basic PDU is a versatile no-frills unit for data centers, server rooms and network wiring closets. Perfectly suited for high-density IT environments, the PDUH32HV19 features four rear C19 outlets. The IEC 309 32A Blue (2P+E) input plug with 3.6 m cord connects to your facility's compatible AC power source, generator or protected UPS to distribute power to connected equipment.

The switchless design prevents an accidental shutdown, which could lead to costly downtime. Dual 20A circuit breakers protect connected equipment from dangerous overloads. The reversible all-metal housing supports a variety of mounting options, including 1U horizontal or 0U vertical mounting in EIA-standard 19-inch racks, under a counter or on a wall or workbench.

Features

Reliable Single-Phase 32A 230V Power Distribution

- Ideal no-frills PDU for data centers, server rooms and network wiring closets
- 4 rear C19 outlets
- IEC 309 32A Blue (2P+E) input with 3.6 m power cord
- Rear-panel grounding lug
- Dual 20A circuit breakers protect against overloads

Switchless Design

- Prevents accidental shutdowns and costly downtime

Highlights

- IEC 309 32A Blue (2P+E) input with 3.6 m power cord
- 4 rear C19 outlets
- Switchless design prevents accidental shutdown
- Reversible all-metal housing
- Dual 20A circuit breakers protect against overloads

Package Includes

- PDUH32HV19 7.4kW Single-Phase 230V Basic PDU
- Mounting hardware
- Owner's manual



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Versatile Installation Options

- Reversible all-metal housing faces front or rear in rack
- Supports 1U horizontal or 0U vertical mounting in EIA-standard 19 in. racks
- Also mounts on wall, workbench or under a counter

Specifications

OVERVIEW	
UPC Code	037332183200
PDU Type	Basic
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	32A 230V
Maximum Input Amps	32
PDU Plug Type	IEC-309 32A BLUE (2P+E)
Input Phase	Single-Phase
Input Cord Length (ft.)	12
Input Cord Length (m)	3.66
OUTPUT	
Output Capacity Details	7.7kW (240V), 7.4kW (230V), 7kW (220V), 6.4kW (200V) / 32A total capacity; 16A max per breakered outlet bank; 16A max per C19 outlet
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) C19
Output Nominal Voltage	200; 220; 230; 240
Overload Protection	Two 20A circuit breakers protect 2 outlets each
USER INTERFACE, ALERTS & CONTROLS	
Switches	n/a
PHYSICAL	
Form Factors Supported	1U rackmount, 0U vertical mount, wallmount and under-counter
Material of Construction	Metal
Minimum Device Depth (cm)	17.27
Minimum Device Depth (in.)	6.8



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Minimum Device Depth (mm)	173
PDU Form Factor	Horizontal (1U)
Shipping Dimensions (hwd / cm)	7.62 x 51.44 x 28.58
Shipping Dimensions (hwd / in.)	3.00 x 20.25 x 11.25
Shipping Weight (kg)	3.21
Shipping Weight (lbs.)	7.07
Unit Dimensions (hwd / cm)	4.5 x 44.5 x 9.53
Unit Dimensions (hwd / in.)	1.75 x 17.5 x 3.75
Unit Weight (kg)	2.87
Unit Weight (lbs.)	6.32
ENVIRONMENTAL	
Storage Temperature Range	-30°C to +50°C (-22°F to +122°F)
Relative Humidity	5 to 95% non-condensing
SPECIAL FEATURES	
TVSS Grounding	Rear grounding lug
STANDARDS & COMPLIANCE	
Certifications	Tested to CE (EN 60950-1), CE Class A, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>