




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.31 – 2.08 mm²**

Mating Tab Width: **2.8 mm, 3.18 mm** [.11 in, .125 in]

Mating Tab Thickness: **.51 mm** [.02 in]

Features

Product Type Features

Terminal Features	Wire Stop
Insertion Force	Normal

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Electrical Characteristics

Voltage Rating	600 V
----------------	-------

Body Features

Insulation Material	Nylon
---------------------	-------

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	2.8 mm, 3.18 mm[.11 in][.125 in]
Mating Tab Thickness	.51 mm[.02 in]
Terminal Orientation	Straight



Contact Base Material	Brass
Terminal Plating Material	Tin
Crimp Type	F-Crimp
Barrel Type	Closed

Termination Features

Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	22.01 mm[.865 in]
Compatible Insulation Diameter Range	6.6 mm[.26 in]
Terminal Material Thickness	.41 mm[.016 in]
Wire Size	1.31 – 2.08 mm²

Usage Conditions

Insulation Option	Fully Insulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	UL
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	2000
Packaging Method	Strip/Reel

Other

Barrel Color	Blue
--------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 90391-3
DIES ULTRA-FAST FASTON 16-14 DIE SET

TE Part # 58078-3
TETRA CRIMP FRAME W/O DIES

TE Part # 58628-1
PROCRIMP T&D 26-14 ULTRAFAST

TE Part # 7-2151699-7
OCEAN_2.0_SPARE_PART_KIT-205D

TE Part # 2151699-2
OCEAN_2.0_Applicator-S-205D-RSA

TE Part # 58628-2
PROCRIMP DIESET 26-14 ULTRAFAST

Also in the Series | **Ultra-Fast 110**



Quick Disconnects(14)


Customers Also Bought



TE Part #63941-1
RCPT 187 FL/FAST AMVR 0157TPBR



TE Part #63942-1
RCPT,187 FL/FAST/AMVR 0157TPBR



TE Part #2-459866-4
ANVIL, COMB. AMPLIVAR



TE Part #1217955-1
.187 FAST FL AMVAR 0157 TPBR



TE Part #1742685-1
FASTON 187 TERMINAL-FLAG REC
18 AWG TPBR




TE Part #2217002-2
G II CE THRU-SPLICE TERMINATOR,
W/CQM



TE Part #1-2273110-5
M8 strgt socket to M12 strgt plug AA



TE Part #2-2324579-0
HOUSING, PLUG, 20P,DUAL ROW,
EP2.5



TE Part #679326-6
SHEAR, GUIDE



TE Part #1338209-2
BLADE, SLUG

Documents

Product Drawings

ULTRA-FAST 110/125 ASY REC 16-14AWG TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-520370-2_K.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_3-520370-2_K.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-520370-2_K.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[Agency Approval Document](#)

English