





1.Wiring Diagram.



2.Cable test condition :

Open / Short : 100%

Insulation resistance : 5M ohms

Contact resistance : 2 ohm

Hipot : DC 300V / 1 sec

3.Each pcs with PE polybag.

7	CPPER	COPPER FOIL 20x40mm	1		
6	CPPER	COPPER FOIL 15X40mm	1		
5	CONN	USB3.0 MICRO B MALE G/F BLACK	1	P2	
4	PVC	45P PVC BLACK OVERMOLD	25g		
3	PE	LLDPE 500026 6201	16g		
2	CONN	USB3.0 A/M G/F BLUE	1	P1	
1	CABLE	《28AWG (7/0.12TC) *1P+D(7/0.10TC)+AL+M》*2+28AWG (7/0.12TC) *1P+24AWG(7/0.2TC)*2C+A+D+B (96/0.12AM) OD5.5 BLACK	1	500mm	
NO.	PART NO.	DESCRIPTION	QTY	UNIT/REF	
BILL OF MATERIAL					

B	20001	ADD COPPER FOIL	2020/05/07
A		INITIAL RELEASE	2014/08/28
REV	ECN#	DESCRIPTION	DATE
		P/N: 103-1092-BL-00050	REV B
		CABLE USB3.0 A/M TO MICRO B MALE	
DRAWN	WENC	DATE	08/24/14
CHECKED	EDWIN	CUSTOMER P/N:	
APPROVAL		CUSTOMER:	
		SHEET 1 OF 1	