IXYS


HiPerFET™ Power MOSFETs Q-Class

IXFN 44N50Q
IXFN 48N50Q


V_{DSS}	I_{D25}	$R_{DS(on)}$
500 V	44 A	120 mΩ
500 V	48 A	100 mΩ

$t_{rr} \leq 250$ ns

N-Channel Enhancement Mode
Avalanche Rated, Low Q_g, High dv/dt



miniBLOC, SOT-227 B (IXFN)
E153432



G = Gate D = Drain
S = Source

Either Source terminal at miniBLOC can be used as Main or Kelvin Source

Symbol	Test Conditions		Maximum Ratings	
V_{DSS}	T_J = 25°C to 150°C		500	V
V_{DGR}	T_J = 25°C to 150°C; R_{GS} = 1 MΩ		500	V
V_{GS}	Continuous		±20	V
V_{GSM}	Transient		±30	V
I_{D25}	T_C = 25°C	44N50	44	A
		48N50	48	A
I_{DM}	T_C = 25°C, pulse width limited by T_{JM}	44N50	176	A
		48N50	192	A
I_{AR}	T_C = 25°C		48	A
E_{AR}	T_C = 25°C		60	mJ
E_{AS}			2.5	mJ
dv/dt	$I_S \leq I_{DM}$, di/dt ≤ 100 A/µs, $V_{DD} \leq V_{DSS}$, $T_J \leq 150°C$, R_G = 2 Ω		15	V/ns
P_D	T_C = 25°C		500	W
T_J			-55 to +150	°C
T_{JM}			150	°C
T_{stg}			-55 to +150	°C
V_{ISOL}	50/60 Hz, RMS t = 1 min		2500	V~
	$I_{ISOL} \leq$ 1 mA t = 1 s		3000	V~
M_d	Mounting torque		1.5/13	Nm/lb.in.
	Terminal connection torque		1.5/13	Nm/lb.in.
Weight			30	g

Symbol	Test Conditions		Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
V_{DSS}	V_{GS} = 0 V, I_D = 1 mA		500			V
$V_{GS(th)}$	$V_{DS} = V_{GS}$, I_D = 4 mA		2.0		4.0	V
I_{GSS}	V_{GS} = ±20 V_{DC}, V_{DS} = 0				±100	nA
I_{DSS}	$V_{DS} = V_{DSS}$	T_J = 25°C			100	µA
	V_{GS} = 0 V	T_J = 125°C			2	mA
$R_{DS(on)}$	V_{GS} = 10 V, I_D = 0.5 I_{D25}	44N50			120	Ω
		48N50			100	Ω
	Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %					

Features
- IXYS advanced low Q_g process
- Low gate charge and capacitances
  - easier to drive
  -faster switching
- Unclamped Inductive Switching (UIS) rated
- Low $R_{DS\ (on)}$
- Fast intrinsic diode
- International standard package
- miniBLOC with Aluminium nitride isolation for low thermal resistance
- Low terminal inductance (<10 nH) and stray capacitance to heatsink (<35pf)
- Molding epoxies meet UL 94 V-0 flammability classification

Applications
- DC-DC converters
- Battery chargers
- Switched-mode and resonant-mode power supplies
- DC choppers
- Temperature and lighting controls

Advantages
- Easy to mount
- Space savings
- High power density

© 2003 IXYS All rights reserved


Downloaded from Arrow.com.

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
g_{fs}	V_{DS} = 20 V; I_D = 0.5 • I_{D25}, pulse test	30	42		S
C_{iss}	V_{GS} = 0 V, V_{DS} = 25 V, f = 1 MHz		7000		pF
C_{oss}			960		pF
C_{rss}			230		pF
$t_{d(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25} R_G = 4.7 Ω (External),		33		ns
t_r			22		ns
$t_{d(off)}$			75		ns
t_f			10		ns
$Q_{g(on)}$	V_{GS} = 10 V, V_{DS} = 0.5 • V_{DSS}, I_D = 0.5 • I_{D25}		190		nC
Q_{gs}			40		nC
Q_{gd}			86		nC
R_{thJC}				0.26	K/W
R_{thCK}			0.05		K/W

Source-Drain Diode

Symbol	Test Conditions	Characteristic Values (T_J = 25°C, unless otherwise specified) min.	typ.	max.	
I_S	V_{GS} = 0 V			48	A
I_{SM}	Repetitive; pulse width limited by T_{JM}			192	A
V_{SD}	$I_F = I_S$, V_{GS} = 0 V, Pulse test, t ≤ 300 µs, duty cycle d ≤ 2 %			1.5	V
t_{rr}	I_F = 25A, -di/dt = 100 A/µs, V_R = 100 V			250	ns
Q_{RM}			1.0		µC
I_{RM}			10		A

miniBLOC, SOT-227 B



M4 screws (4x) supplied

Dim.	Millimeter Min.	Max.	Inches Min.	Max.
A	31.50	31.88	1.240	1.255
B	7.80	8.20	0.307	0.323
C	4.09	4.29	0.161	0.169
D	4.09	4.29	0.161	0.169
E	4.09	4.29	0.161	0.169
F	14.91	15.11	0.587	0.595
G	30.12	30.30	1.186	1.193
H	38.00	38.23	1.496	1.505
J	11.68	12.22	0.460	0.481
K	8.92	9.60	0.351	0.378
L	0.76	0.84	0.030	0.033
M	12.60	12.85	0.496	0.506
N	25.15	25.42	0.990	1.001
O	1.98	2.13	0.078	0.084
P	4.95	5.97	0.195	0.235
Q	26.54	26.90	1.045	1.059
R	3.94	4.42	0.155	0.174
S	4.72	4.85	0.186	0.191
T	24.59	25.07	0.968	0.987
U	-0.05	0.1	-0.002	0.004

IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 6,259,123B1 6,306,728B1 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025 6,404,065B1 6,162,665 6,534,343

Downloaded from Arrow.com.

Fig. 1. Output Characteristics @ 25 Deg. C




Fig. 2. Extended Output Characteristics @ 25 deg. C




Fig. 3. Output Characteristics @ 125 Deg. C




Fig. 4. $R_{DS(on)}$ Normalized to I_{D25} Value vs. Junction Temperature




Fig. 5. $R_{DS(on)}$ Normalized to I_{D25} Value vs. I_D





Fig. 6. Drain Current vs. Case Temperature



© 2003 IXYS All rights reserved

Downloaded from Arrow.com.

Fig. 7. Input Admittance




Fig. 8. Transconductance




Fig. 9. Source Current vs. Source-To-Drain Voltage




Fig. 10. Gate Charge




Fig. 11. Capacitance





Fig. 12. Maximum Transient Thermal Resistance



IXYS reserves the right to change limits, test conditions, and dimensions.

IXYS MOSFETs and IGBTs are covered by one or more of the following U.S. patents: 4,835,592 4,881,106 5,017,508 5,049,961 5,187,117 5,486,715 6,306,728B1 6,259,123B1 6,306,728B1 4,850,072 4,931,844 5,034,796 5,063,307 5,237,481 5,381,025 6,404,065B1 6,162,665 6,534,343

Downloaded from Arrow.com.



Disclaimer Notice - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

Downloaded from Arrow.com.